

185A-195A.G - LONG HALF-ROUND NOSE PLIERS




Standards :

NF ISO 5745, ISO 5745, DIN ISO 5745, ASME B107.500

Description :

- Narrow, finely serrated tips with side cutting edges.
- Cutting edges for copper and hard steel wire to a maximum specification of 1.6mm 160 kg/mm².
- 183AE: straight long thin nose with wire stripping & gripping 1.5mm² - 2.5mm² - 4mm².
- 185: straight nose.
- 195: 40° angled nose.
- High durability carbon alloy steel, with induction hardened cutting edges.
- Mono-Material ergonomic grips maintaining accessibility benefits of classic dip grips, resistant to workshop chemical agents
- Varnish finish to help prevent rusting.

References :

	B [MM]	C [MM]	D [MM]	E [MM]	E1 [MM]	L [MM]	[G]
195A.16G	17	50	2,5	3,0	9	160	177
195A.20G	18	69	2,9	3,6	9	200	192
185A.20G	18	75	2,9	3,6	9	200	192