

## AT.VE - PROTWIST® 1,000 VOLT INSULATED SCREWDRIVERS FOR SLOTTED-HEAD SCREWS




### Standards :


NF ISO 2380-1, NF ISO 2380-2, NF EN 60900, ISO 2380-1, ISO 2380-2, EN 60900, DIN ISO 2380-1, DIN ISO 2380-2, DIN EN 60900ASME B107.600


### Description :

- For improved safety, each screwdriver is tested individually at 10,000 Volt for 10 seconds VDE approved.
- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.
- Milled blade: --> 5.5 mm included.
- Fillet blade: 6.5 --> 12 mm.



### References :

	A [MM]	D [MM]	E [MM]	L [MM]	L1 [MM]	L2 [MM]	L3 [MM]	[G]
AT2X75VE	2,0	19	0,4	170	40	95	18	23
AT2.5x75VE	2,5	25	0,4	178	75	103	18	32
AT3X75VE	3,0	25	0,5	178	75	103	18	38
AT3X100VE	3,0	25	0,5	202	100	103	18	39
AT4X150VE	4,0	30	0,8	260	150	110	18	53
AT5.5x125VE	5,5	30	1,0	235	125	110	18	88
AT5.5x200VE	5,5	30	1,0	310	200	110	18	106

	A [MM]	D [MM]	E [MM]	L [MM]	L1 [MM]	L2 [MM]	L3 [MM]	[G]
AT6.5x200VE	6,5	36	1,2	320	200	120	18	170
AT8X200VE	8,0	40	1,2	325	200	125	18	180
AT12X250VE	12,0	40	2,0	375	250	125	18	360
AT2.5X50VE	2,5	25	0,4	153	50	103	18	30
AT10X200VE	10,0	40	1,6	325	200	125	18	240
AT3.5x100VE	3,5	25	0,6	204	100	104	18	44
AT4X100VE	4,0	30	0,8	210	100	110	18	48
AT6.5x150VE	6,5	36	1,2	270	150	120	18	120
AT8X150VE	8,0	40	1,2	275	150	125	18	160
AT3.5x75VE	3,5	25	0,6	179	75	104	18	42
AT5.5x150VE	5,5	30	1,0	260	150	110	18	92