

DS 150 (619150000) Bench Grinder
(220-240 V / 50 Hz); Cardboard box

Order no. 619150000
EAN 4007430193285



Product may differ from image



- Small and space-saving workshop machine
- Low-noise and low-vibration, maintenance-free induction motor
- Motor for single phase alternating current
- Protective cover bayonet lock for quick and simple wheel change
- Large spark protection guards for eye protection
- Vibration-dampening rubber feet for safe support

Technical data**Characteristics**

Grinding wheels (Ø x thickness x bore)	150 x 20 x 20 mm
No-load speed	2980 rpm
Mains voltage	220 - 240 V
Rated input power	350 W
Output power	200 W
Breakdown torque	1.1 Nm
Weight	9.5 kg
Cable length	2 m

Scope of delivery

Regular aluminium oxide grinding discs 36 P and 60 N
Spark protection glasses
Work piece support
Hexagonal wrench