

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GRM0225C1HR20WA03	0402M/01005	C0G	50Vdc	0.2pF	±0.05pF	0.22max	20
2	GRM0225C1HR30WA03	0402M/01005	C0G	50Vdc	0.3pF	±0.05pF	0.22max	20
3	GRM0225C1HR40WA03	0402M/01005	C0G	50Vdc	0.4pF	±0.05pF	0.22max	20
4	GRM0225C1HR50WA03	0402M/01005	C0G	50Vdc	0.5pF	±0.05pF	0.22max	20
5	GRM0225C1HR60WA03	0402M/01005	C0G	50Vdc	0.6pF	±0.05pF	0.22max	20
6	GRM0225C1HR70WA03	0402M/01005	C0G	50Vdc	0.7pF	±0.05pF	0.22max	20
7	GRM0225C1HR80WA03	0402M/01005	C0G	50Vdc	0.8pF	±0.05pF	0.22max	20
8	GRM0225C1HR90WA03	0402M/01005	C0G	50Vdc	0.9pF	±0.05pF	0.22max	20
9	GRM0225C1H1R0WA03	0402M/01005	C0G	50Vdc	1.0pF	±0.05pF	0.22max	100
10	GRM0225C1H1R1BA03	0402M/01005	C0G	50Vdc	1.1pF	±0.1pF	0.22max	20
11	GRM0225C1H1R2BA03	0402M/01005	C0G	50Vdc	1.2pF	±0.1pF	0.22max	20
12	GRM0225C1H1R3BA03	0402M/01005	C0G	50Vdc	1.3pF	±0.1pF	0.22max	20
13	GRM0225C1H1R4BA03	0402M/01005	C0G	50Vdc	1.4pF	±0.1pF	0.22max	20
14	GRM0225C1H1R5BA03	0402M/01005	C0G	50Vdc	1.5pF	±0.1pF	0.22max	20
15	GRM0225C1H1R6BA03	0402M/01005	C0G	50Vdc	1.6pF	±0.1pF	0.22max	20
16	GRM0225C1H1R7BA03	0402M/01005	C0G	50Vdc	1.7pF	±0.1pF	0.22max	20
17	GRM0225C1H1R8BA03	0402M/01005	C0G	50Vdc	1.8pF	±0.1pF	0.22max	20
18	GRM0225C1H1R9BA03	0402M/01005	C0G	50Vdc	1.9pF	±0.1pF	0.22max	20
19	GRM0225C1H2R0BA03	0402M/01005	C0G	50Vdc	2.0pF	±0.1pF	0.22max	20
20	GRM0225C1H2R1BA03	0402M/01005	C0G	50Vdc	2.1pF	±0.1pF	0.22max	20
21	GRM0225C1H2R2BA03	0402M/01005	C0G	50Vdc	2.2pF	±0.1pF	0.22max	20
22	GRM0225C1H2R3BA03	0402M/01005	C0G	50Vdc	2.3pF	±0.1pF	0.22max	20
23	GRM0225C1H2R4BA03	0402M/01005	C0G	50Vdc	2.4pF	±0.1pF	0.22max	20
24	GRM0225C1H2R5BA03	0402M/01005	C0G	50Vdc	2.5pF	±0.1pF	0.22max	20
25	GRM0225C1H2R6BA03	0402M/01005	C0G	50Vdc	2.6pF	±0.1pF	0.22max	20
26	GRM0225C1H2R7BA03	0402M/01005	C0G	50Vdc	2.7pF	±0.1pF	0.22max	20
27	GRM0225C1H2R8BA03	0402M/01005	C0G	50Vdc	2.8pF	±0.1pF	0.22max	20
28	GRM0225C1H2R9BA03	0402M/01005	C0G	50Vdc	2.9pF	±0.1pF	0.22max	20
29	GRM0225C1H3R0BA03	0402M/01005	C0G	50Vdc	3.0pF	±0.1pF	0.22max	20
30	GRM0225C1H3R1BA03	0402M/01005	C0G	50Vdc	3.1pF	±0.1pF	0.22max	20
31	GRM0225C1H3R2BA03	0402M/01005	C0G	50Vdc	3.2pF	±0.1pF	0.22max	20
32	GRM0225C1H3R3BA03	0402M/01005	C0G	50Vdc	3.3pF	±0.1pF	0.22max	20
33	GRM0225C1H3R4BA03	0402M/01005	C0G	50Vdc	3.4pF	±0.1pF	0.22max	20

34	GRM0225C1H3R5BA03	0402M/01005	COG	50Vdc	3.5pF	±0.1pF	0.22max	20
35	GRM0225C1H3R6BA03	0402M/01005	COG	50Vdc	3.6pF	±0.1pF	0.22max	20
36	GRM0225C1H3R7BA03	0402M/01005	COG	50Vdc	3.7pF	±0.1pF	0.22max	20
37	GRM0225C1H3R8BA03	0402M/01005	COG	50Vdc	3.8pF	±0.1pF	0.22max	20
38	GRM0225C1H3R9BA03	0402M/01005	COG	50Vdc	3.9pF	±0.1pF	0.22max	20
39	GRM0225C1H4R0BA03	0402M/01005	COG	50Vdc	4.0pF	±0.1pF	0.22max	20
40	GRM0225C1H4R1BA03	0402M/01005	COG	50Vdc	4.1pF	±0.1pF	0.22max	20
41	GRM0225C1H4R2BA03	0402M/01005	COG	50Vdc	4.2pF	±0.1pF	0.22max	20
42	GRM0225C1H4R3BA03	0402M/01005	COG	50Vdc	4.3pF	±0.1pF	0.22max	20
43	GRM0225C1H4R4BA03	0402M/01005	COG	50Vdc	4.4pF	±0.1pF	0.22max	20
44	GRM0225C1H4R5BA03	0402M/01005	COG	50Vdc	4.5pF	±0.1pF	0.22max	20
45	GRM0225C1H4R6BA03	0402M/01005	COG	50Vdc	4.6pF	±0.1pF	0.22max	20
46	GRM0225C1H4R7BA03	0402M/01005	COG	50Vdc	4.7pF	±0.1pF	0.22max	20
47	GRM0225C1H4R8BA03	0402M/01005	COG	50Vdc	4.8pF	±0.1pF	0.22max	20
48	GRM0225C1H4R9BA03	0402M/01005	COG	50Vdc	4.9pF	±0.1pF	0.22max	20
49	GRM0225C1H5R0BA03	0402M/01005	COG	50Vdc	5.0pF	±0.1pF	0.22max	20
50	GRM0225C1H5R1BA03	0402M/01005	COG	50Vdc	5.1pF	±0.1pF	0.22max	20
51	GRM0225C1H5R6BA03	0402M/01005	COG	50Vdc	5.6pF	±0.1pF	0.22max	20
52	GRM0225C1H6R2BA03	0402M/01005	COG	50Vdc	6.2pF	±0.1pF	0.22max	20
53	GRM0225C1H6R8BA03	0402M/01005	COG	50Vdc	6.8pF	±0.1pF	0.22max	20
54	GRM0225C1H7R5BA03	0402M/01005	COG	50Vdc	7.5pF	±0.1pF	0.22max	20
55	GRM0225C1H8R2BA03	0402M/01005	COG	50Vdc	8.2pF	±0.1pF	0.22max	20
56	GRM0225C1H9R1BA03	0402M/01005	COG	50Vdc	9.1pF	±0.1pF	0.22max	20
57	GRM0225C1H100GA03	0402M/01005	COG	50Vdc	10pF	±2%	0.22max	100
58	GRM0225C1H120GA03	0402M/01005	COG	50Vdc	12pF	±2%	0.22max	20
59	GRM0225C1H150GA03	0402M/01005	COG	50Vdc	15pF	±2%	0.22max	20
60	GRM0225C1H180GA02	0402M/01005	COG	50Vdc	18pF	±2%	0.22max	20
61	GRM0225C1H220GA02	0402M/01005	COG	50Vdc	22pF	±2%	0.22max	20
62	GRM0225C1H270GA02	0402M/01005	COG	50Vdc	27pF	±2%	0.22max	20
63	GRM0225C1H330GA02	0402M/01005	COG	50Vdc	33pF	±2%	0.22max	20
64	GRM0225C1H390GA02	0402M/01005	COG	50Vdc	39pF	±2%	0.22max	20
65	GRM0225C1H470GA02	0402M/01005	COG	50Vdc	47pF	±2%	0.22max	20
66	GRM0225C1H560GA02	0402M/01005	COG	50Vdc	56pF	±2%	0.22max	20
67	GRM0225C1H680GA02	0402M/01005	COG	50Vdc	68pF	±2%	0.22max	20
68	GRM0225C1H820GA02	0402M/01005	COG	50Vdc	82pF	±2%	0.22max	20
69	GRM0225C1H101GA02	0402M/01005	COG	50Vdc	100pF	±2%	0.22max	100
70	GRM0225C1E221GA02	0402M/01005	COG	25Vdc	220pF	±2%	0.22max	20