

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GRM0335C1HR10WA01	0603M/0201	C0G	50Vdc	0.1pF	±0.05pF	0.33max	20
2	GRM0335C1HR20BA01	0603M/0201	C0G	50Vdc	0.2pF	±0.1pF	0.33max	20
3	GRM0335C1HR30BA01	0603M/0201	C0G	50Vdc	0.3pF	±0.1pF	0.33max	20
4	GRM0335C1HR40BA01	0603M/0201	C0G	50Vdc	0.4pF	±0.1pF	0.33max	20
5	GRM0335C1HR50BA01	0603M/0201	C0G	50Vdc	0.5pF	±0.1pF	0.33max	20
6	GRM0335C1HR60BA01	0603M/0201	C0G	50Vdc	0.6pF	±0.1pF	0.33max	20
7	GRM0335C1HR70BA01	0603M/0201	C0G	50Vdc	0.7pF	±0.1pF	0.33max	20
8	GRM0335C1HR80BA01	0603M/0201	C0G	50Vdc	0.8pF	±0.1pF	0.33max	20
9	GRM0335C1HR90BA01	0603M/0201	C0G	50Vdc	0.9pF	±0.1pF	0.33max	20
10	GRM0335C1H1R0CA01	0603M/0201	C0G	50Vdc	1.0pF	±0.25pF	0.33max	100
11	GRM0335C1H1R1CA01	0603M/0201	C0G	50Vdc	1.1pF	±0.25pF	0.33max	20
12	GRM0335C1H1R2CA01	0603M/0201	C0G	50Vdc	1.2pF	±0.25pF	0.33max	20
13	GRM0335C1H1R3CA01	0603M/0201	C0G	50Vdc	1.3pF	±0.25pF	0.33max	20
14	GRM0335C1H1R4CA01	0603M/0201	C0G	50Vdc	1.4pF	±0.25pF	0.33max	20
15	GRM0335C1H1R5CA01	0603M/0201	C0G	50Vdc	1.5pF	±0.25pF	0.33max	20
16	GRM0335C1H1R6CA01	0603M/0201	C0G	50Vdc	1.6pF	±0.25pF	0.33max	20
17	GRM0335C1H1R7CA01	0603M/0201	C0G	50Vdc	1.7pF	±0.25pF	0.33max	20
18	GRM0335C1H1R8CA01	0603M/0201	C0G	50Vdc	1.8pF	±0.25pF	0.33max	20
19	GRM0335C1H1R9CA01	0603M/0201	C0G	50Vdc	1.9pF	±0.25pF	0.33max	20
20	GRM0335C1H2R0CA01	0603M/0201	C0G	50Vdc	2.0pF	±0.25pF	0.33max	20
21	GRM0335C1H2R1CA01	0603M/0201	C0G	50Vdc	2.1pF	±0.25pF	0.33max	20
22	GRM0335C1H2R2CA01	0603M/0201	C0G	50Vdc	2.2pF	±0.25pF	0.33max	20
23	GRM0335C1H2R3CA01	0603M/0201	C0G	50Vdc	2.3pF	±0.25pF	0.33max	20
24	GRM0335C1H2R4CA01	0603M/0201	C0G	50Vdc	2.4pF	±0.25pF	0.33max	20
25	GRM0335C1H2R5CA01	0603M/0201	C0G	50Vdc	2.5pF	±0.25pF	0.33max	20
26	GRM0335C1H2R6CA01	0603M/0201	C0G	50Vdc	2.6pF	±0.25pF	0.33max	20
27	GRM0335C1H2R7CA01	0603M/0201	C0G	50Vdc	2.7pF	±0.25pF	0.33max	20
28	GRM0335C1H2R8CA01	0603M/0201	C0G	50Vdc	2.8pF	±0.25pF	0.33max	20
29	GRM0335C1H2R9CA01	0603M/0201	C0G	50Vdc	2.9pF	±0.25pF	0.33max	20
30	GRM0335C1H3R0CA01	0603M/0201	C0G	50Vdc	3.0pF	±0.25pF	0.33max	20
31	GRM0335C1H3R3CA01	0603M/0201	C0G	50Vdc	3.3pF	±0.25pF	0.33max	20
32	GRM0335C1H3R6CA01	0603M/0201	C0G	50Vdc	3.6pF	±0.25pF	0.33max	20
33	GRM0335C1H3R9CA01	0603M/0201	C0G	50Vdc	3.9pF	±0.25pF	0.33max	20

34	GRM0335C1H4R3CA01	0603M/0201	COG	50Vdc	4.3pF	±0.25pF	0.33max	20
35	GRM0335C1H4R7CA01	0603M/0201	COG	50Vdc	4.7pF	±0.25pF	0.33max	20
36	GRM0335C1H5R1CA01	0603M/0201	COG	50Vdc	5.1pF	±0.25pF	0.33max	20
37	GRM0335C1H5R6CA01	0603M/0201	COG	50Vdc	5.6pF	±0.25pF	0.33max	20
38	GRM0335C1H6R2CA01	0603M/0201	COG	50Vdc	6.2pF	±0.25pF	0.33max	20
39	GRM0335C1H6R8CA01	0603M/0201	COG	50Vdc	6.8pF	±0.25pF	0.33max	20
40	GRM0335C1H7R5CA01	0603M/0201	COG	50Vdc	7.5pF	±0.25pF	0.33max	20
41	GRM0335C1H8R2CA01	0603M/0201	COG	50Vdc	8.2pF	±0.25pF	0.33max	20
42	GRM0335C1H9R1CA01	0603M/0201	COG	50Vdc	9.1pF	±0.25pF	0.33max	20
43	GRM0335C1H100JA01	0603M/0201	COG	50Vdc	10pF	±5%	0.33max	20
44	GRM0335C1H120JA01	0603M/0201	COG	50Vdc	12pF	±5%	0.33max	20
45	GRM0335C1H150JA01	0603M/0201	COG	50Vdc	15pF	±5%	0.33max	20
46	GRM0335C1H180JA01	0603M/0201	COG	50Vdc	18pF	±5%	0.33max	20
47	GRM0335C1H220JA01	0603M/0201	COG	50Vdc	22pF	±5%	0.33max	20
48	GRM0335C1H270JA01	0603M/0201	COG	50Vdc	27pF	±5%	0.33max	20
49	GRM0335C1H330JA01	0603M/0201	COG	50Vdc	33pF	±5%	0.33max	20
50	GRM0335C1H390JA01	0603M/0201	COG	50Vdc	39pF	±5%	0.33max	20
51	GRM0335C1H470JA01	0603M/0201	COG	50Vdc	47pF	±5%	0.33max	20
52	GRM0335C1H560JA01	0603M/0201	COG	50Vdc	56pF	±5%	0.33max	20
53	GRM0335C1H680JA01	0603M/0201	COG	50Vdc	68pF	±5%	0.33max	20
54	GRM0335C1H820JA01	0603M/0201	COG	50Vdc	82pF	±5%	0.33max	20
55	GRM0335C1H101JA01	0603M/0201	COG	50Vdc	100pF	±5%	0.33max	100
56	GRM0335C1H121JA01	0603M/0201	COG	50Vdc	120pF	±5%	0.33max	20
57	GRM0335C1H151JA01	0603M/0201	COG	50Vdc	150pF	±5%	0.33max	20
58	GRM0335C1H181JA01	0603M/0201	COG	50Vdc	180pF	±5%	0.33max	20
59	GRM0335C1H221JA01	0603M/0201	COG	50Vdc	220pF	±5%	0.33max	20
60	GRM0335C1H271JE01	0603M/0201	COG	50Vdc	270pF	±5%	0.33max	20
61	GRM0335C1H331JE01	0603M/0201	COG	50Vdc	330pF	±5%	0.33max	20
62	GRM0335C1H391JE01	0603M/0201	COG	50Vdc	390pF	±5%	0.33max	20
63	GRM0335C1H471JE01	0603M/0201	COG	50Vdc	470pF	±5%	0.33max	20
64	GRM0335C1H561JE01	0603M/0201	COG	50Vdc	560pF	±5%	0.33max	20
65	GRM0335C1H681JE01	0603M/0201	COG	50Vdc	680pF	±5%	0.33max	20
66	GRM0335C1H821JE01	0603M/0201	COG	50Vdc	820pF	±5%	0.33max	20
67	GRM0335C1H102JE01	0603M/0201	COG	50Vdc	1000pF	±5%	0.33max	100