























■ Features

- Constant Current mode output with multiple levels selectable by dip switch
- Emergency lighting application is available according to IEC61347-2-13
- · Built-in active PFC function and class II design
- Standby power consumption < 0.5W
- Functions: DALI interface(logarithm or linear dimming curve selectable), push dimming synchronization up to 10units
- · 3 years warranty


Applications

- · LED indoor lighting
- · LED office lighting
- · LED commercial lighting
- LED panel lighting

Description

LCM-40DA series is a 40W AC/DC constant current mode output LED driver featuring the multiple levels selectable by dip switch and the DALI interface with the compliance to IEC62386. LCM-40DA operates from $180\sim295$ VAC and offers different current levels ranging between 350mA and 1050mA. Thanks to the high efficiency up to 91%, with the fanless design, the entire series is able to operate for $-30^{\circ}\text{C} \sim +90^{\circ}\text{C}$ case temperature under free air convection. In addition, LCM-40DA is equipped with push dimming and synchronization functions, so as to provide the optimal design flexibility for LED lighting system.

■ Model Encoding



Type	Function	Note
Blank	standby power consumption <0.5W	In Stock
AUX	standby power consumption <1.2W and Auxiliary DC output(12V/50mA)	By request



40W Multiple-Stage Constant Current Mode LED Driver


LCM-40DA series

SPECIFICATION

MODEL		LCM-40							
		Current level selectable via DIP switch, please refer to "DIP SWITCH TABLE" section							
	CURRENT LEVEL	350mA	500mA	600mA	700mA(default)	900mA	1050mA		
	RATED POWER	42W				_			
CUTDUT	DC VOLTAGE RANGE	2 ~ 100V	2 ~ 80V	2 ~ 67V	2 ~ 57V	2 ~ 45V	2~40V		
OUTPUT	OPEN CIRCUIT VOLTAGE (max.)	110V		<u> </u>	65V	-			
	CURRENT RIPPLE Note.5	5.0% max. @rate	d current						
	CURRENT TOLERANCE	±5%							
	AUXILIARY DC OUTPUT		iation 11.4~12.6V)	@50mA for AUX-Type	only				
	SETUD TIME Note.3	500ms / 230VAC		<u> </u>	,				
	VOLTAGE RANGE Note.2	180 ~ 295VAC	254 ~ 417VDC						
	FREQUENCY RANGE	(Please refer to "S	STATIC CHARACTE	ERISTIC" section)					
		DE > 0.075/220V	AC DE>0.05/277	VAC@full load					
	POWER FACTOR (Typ.)		F≥0.975/230VAC, PF≥0.95/277VAC@full load Please refer to "POWER FACTOR (PF) CHARACTERISTIC" section)						
	TOTAL HARMONIC DISTORTION	THD< 20%(@load≧75%) (Please refer to "TOTAL HARMONIC DISTORTION(THD)" section)							
INPUT	EFFICIENCY (Typ.) Note.4	91%							
	AC CURRENT (Typ.)	0.23A/230VAC	0.2A/277VAC						
	INRUSH CURRENT (Typ.)	COLD START 20A	A(twidth=260µs meas	sured at 50% Ipeak) at 2	30VAC; Per NEMA 410				
	MAX. No. of PSUs on 16A CIRCUIT BREAKER	26 units (circuit b	reaker of type B) / 4	4 units (circuit break	er of type C) at 230VAC				
	LEAKAGE CURRENT	<0.5mA / 240VAC							
	STANDBY POWER CONSUMPTION Note.6	<0.5W for Blank-Type, <1.2W for AUX-Type							
	SHORT CIRCUIT	Constant current limiting, recovers automatically after fault condition is removed							
PROTECTION	OVER VOLTAGE	110 ~ 130V Shutdown o/p voltage, re-power on to recover							
	OVER TEMPERATURE	Shutdown o/p vo	ltage,re-power on	to recover					
	DIMMING	Please refer to "	DIMMING OPERA	TION" section					
FUNCTION	SYNCHRONIZATION	Please refer to "	SYNCHRONIZATI	ON OPERATION" sed	tion				
	TEMP. COMPENSATION	By external NTC	, please refer to "T	EMPERATURE COM	PENSATION OPERATIO	N"section			
	WORKING TEMP.	Tcase=-30 ~ +90°	C (Please refer to "	OUTPUT LOAD vs T	EMPERATURE" section)				
	MAX. CASE TEMP.	Tcase=+90°C							
	WORKING HUMIDITY	20 ~ 90% RH non	-condensing						
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~	95% RH						
	TEMP. COEFFICIENT	±0.03%/℃ (0	~50℃)						
	VIBRATION	10 ~ 500Hz, 2G 1	0min./1cycle, perio	d for 60min. each alo	ng X, Y, Z axes				
	SAFETY STANDARDS	GB19510.1, BIS	• • • •	DA2-Type), EAC TP T	ENEC EN61347-1, EN613 C 004 approved; Accordin				
	DALI STANDARDS	IEC62386-101, 1							
SAFETY &	WITHSTAND VOLTAGE		C;I/P-DA:1.5KVAC;	O/P-DA:1.5KVAC					
EMC	ISOLATION RESISTANCE		hms / 500VDC / 25						
	EMC EMISSION Note.7				10%) ; EN61000-3-3; GB1	7625 1 GB17743	FAC TP TC 020		
	EMC IMMUNITY	-		, , ,	ndustry level(surge immur				
	MTBF	193.6K hrs min.	MIL-HDBK-217F		nador y lovol(ourgo mimar	my Emo Emo Erry	, 27,0 11 10 020		
OTHERS	DIMENSION	123.5*81.5*23mm		(200)					
CHERS	PACKING	0.24Kg; 54pcs/1							
NOTE	1. All parameters NOT special 2. De-rating may be needed u 3. Length of set up time is me. 4. Efficiency is measured at 56 5. Current ripple is measured: 6. Standby power consumption 7. The driver is considered as complete installation, the fin 8. The ambient temperature de 9.Based on IEC 62386-101/10 can support for DALI power ※ Product Liability Disclaimer	ly mentioned are r nder low input volt asured at first cold 20mA/80V output s 50%~100% of man n is measured at 1 a component that al equipment man erating of 3.5°C/10 12 DALI power on on function, otherw	neasured at 230V/ages. Please refer start. Turning ON/set by DIP switch. kimum voltage und 80-230VAC. will be operated in ufacturers must re-00m with fanless r timing and interrup vise the set up tim.	to "STATIC CHARA(OFF the driver may I ler rated power delive combination with fina qualify EMC Directive models and of 5°C/10 tion regulations, the s e will be higher than 0	CTERISTIC" sections for ead to increase of the set ry. al equipment. Since EMC e on the complete installa 00m with fan models for et up time needs to test to 5.5 second for DA2-type.	details. t up time. performance will tion again. operating altitude with a DALI control	higher than 2000m(6500		

■ BLOCK DIAGRAM

PFC fosc : 60KHz PWM fosc : 80KHz




■ DIP SWITCH TABLE


LCM-40DA/DA2 is a multiple-stage constant current driver, selection of output current through DIP switch is exhibited below.

lo DIP S.W.	1	2	3	4	5	6
350mA						
500mA	ON					
600mA	ON	ON				
700mA(factory default)	ON	ON	ON			ON
900mA	ON	ON	ON	ON		ON
1050mA	ON	ON	ON	ON	ON	ON

Note: For more current setting, please contact MW's sales.

■ DIMMING OPERATION





※PUSH dimming(primary side)

Action	Action duration	Function
Short push	0.1~1 sec.	Turn ON-OFF the driver
Long push	1.5~10 sec.	Every Long Push changes the dimming direction, dimming up or down
Reset	>11 sec.	Set up the dimming level to 100%


- The factory default dimming level is at 100%.
- If the push action lasts less than 0.05 sec., it will not lead to a change for the status of the driver.
- Up to 10 drivers can perform the PUSH dimming at the same time when utilizing one common push button.
- The maximum length of the cable from the push button to the last driver is 20 meters.
- The additive push button can be connected only between the PUSH terminal, as displayed in the diagram, and AC/L (in brown or black); it will lead to short circuit if it is connected to AC/N.

★DALI interface(primary side; for DA/DA2-Type)

- · Apply DALI signal between DA+ and DA-
- DALI protocol comprises 16 groups and 64 addresses.
- First step is fixed at 6% of output.

■ SYNCHRONIZATION OPERATION

- Synchronization up to 10 drivers (1 master + 9 slaves)
- Dimming operating range: 10%~100%
- Sync cable length : < 5m
- · Sync cable type : Flat cable
- Sync cable cross section area: 22 24 AWG (0.2~0.3mm²)




NOTE: 1. Please make sure all units are set to 100% dimming setting (factory default) before synchronizing.

2. Min. Dimming operating range depends on dimmer setting.

■ TEMPERATURE COMPENSATION OPERATION

LCM-40DA/DA2 have the built-in temperature compensation function; by connecting a temperature sensor (NTC resistor) between the +NTC / -NTC terminal of LCM-40DA/DA2 and the detecting point on the lighting system or the surrounding environment, output current of LCM-40DA/DA2 could be correspondingly changed, based on the sensed temperature, to ensure the long life of LED.



© LCM-40DA/DA2 can still be operated normally when the NTC resistor is not connected and the value of output current will be the current level selected through the DIP switch.

NTC reference:


NTC resistance	Output Current
220K	< 60°C, 100% of the rated current (corresponds to the setting current level) > 60°C, output current begins to reduce, please refer to the curve for details.
330K	<70 $^{\circ}$ C, 100% of the rated current (corresponds to the setting current level) >70 $^{\circ}$ C, output current begins to reduce, please refer to the curve for details.
470K	< 80° C, 100% of the rated current (corresponds to the setting current level) > 80° C, output current begins to reduce, please refer to the curve for details.


Notes: 1. MEAN WELL does not offer the NTC resistor and all the data above are measured by using THINKING TTC03 series.

- $2. \ If other brands of NTC \ resistor \ is \ applied, please \ check \ the \ temperature \ curve \ first.$
- O Dimming and synchronization function of the driver will be invalid when the "temperature compensation" function is in use.




■ OUTPUT LOAD vs TEMPERATURE






■ STATIC CHARACTERISTIC



X De-rating is needed under low input voltage.







Unit:mm

Case No.LCM-60A

■ MECHANICAL SPECIFICATION





Terminal Pin No. Assignment(TB1)(LCM-40DA)


	Pin No.	Assignment	Pin No.	Assignment
	1 AC/L		4	DA+
	2 AC/N		5	DA-
ĺ	3 PUSH			


Terminal Pin No. Assignment(TB1)(LCM-40DA2)

	•	,	/ \
Pin No. Assignmen		Pin No.	Assignment
1	AC/L	4	DA-
2 AC/N			
3	DA+		

※ Terminal Pin No. Assignment(TB3)

,						
Pin No. Assignment		Pin No.	Assignment			
1 +FAN(+AUX)		3	+NTC			
2 -FAN(-AUX)		4	-NTC			





• (tc) : Max. Case Temperature

© Pin1(+FAN) / Pin2(-FAN) is the Auxiliary DC output for the optional model LCM-40DA-AUX; it can be used to drive fan.

★ Terminal Pin No. Assignment(TB5)

Pin No.	Assignment
1	+V
2	-V

※ SYN. Connector(CN101/CN100):JST B2B-XH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1,3	+	JST XHP	JST SXH-001T-P0.6
2,4	-	or equivalent	or equivalent

■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html