





**LOW PROFILE JACKSCREW ASSEMBLY**




| SHELL SIZE      | 9-69                  |                      | 100                   |                      |
|-----------------|-----------------------|----------------------|-----------------------|----------------------|
| AMPHENOL P/N    | HM05-05               | HM05-02              | HM05-15               | HM05-12              |
| P/N CODE        | M5                    | M2                   | M5                    | M2                   |
| MIL-SPEC P/N    | M83513/05-05 (SLOT)   | M83513/05-02 (ALLEN) | M83513/05-15 (SLOT)   | M83513/05-12 (ALLEN) |
| Dim. A          | .258/.235 (6.55/5.97) |                      | .287±.005 (7.29±0.13) |                      |
| Dim. B          | .125 (3.18)           |                      | .187 (4.75)           |                      |
| Dim. C (THREAD) | #2-56 UNC-2A          |                      | #4-40 UNC-2A          |                      |
| Dim. D          | .103/.070 (2.62/1.78) |                      | .098 (2.49)           |                      |
| Dim. E (HEX)    | N/A                   |                      |                       |                      |

**HIGH PROFILE JACKSCREW ASSEMBLY**




| SHELL SIZE      | 9-69                  |                      | 100                   |                      |
|-----------------|-----------------------|----------------------|-----------------------|----------------------|
| AMPHENOL P/N    | HM05-06               | HM05-03              | HM05-16               | HM05-13              |
| P/N CODE        | M6                    | M3                   | M6                    | M3                   |
| MIL-SPEC P/N    | M83513/05-06 (SLOT)   | M83513/05-03 (ALLEN) | M83513/05-16 (SLOT)   | M83513/05-13 (ALLEN) |
| Dim. A          | .258/.235 (6.55/5.97) |                      | .287±.005 (7.29±0.13) |                      |
| Dim. B          | .125 (3.18)           |                      | .187 (4.75)           |                      |
| Dim. C (THREAD) | #2-56 UNC-2A          |                      | #4-40 UNC-2A          |                      |
| Dim. D          | N/A                   |                      |                       |                      |
| Dim. E (HEX)    | N/A                   |                      |                       |                      |


**RETAINING CLIP DETAIL**





**ALLEN HEAD DETAIL**



**SLOT HEAD DETAIL**




**JACKPOST ASSEMBLY**




| SHELL SIZE      | 9-69                  | 100                   |
|-----------------|-----------------------|-----------------------|
| AMPHENOL P/N    | HM05-07               | HM05-17               |
| P/N CODE        | P                     |                       |
| MIL-SPEC P/N    | M83513/05-07          | M83513/05-17          |
| Dim. A          | .190/.185 (4.83/4.70) | .185/.180 (4.70/4.58) |
| Dim. B          | .155 (3.94)           | .170 (4.32)           |
| Dim. C (THREAD) | #2-56 UNC-2A          | #4-40 UNC-2A          |
| Dim. D          | #2-56 UNC-2B          | #4-40 UNC-2B          |
| Dim. E (HEX)    | .125 (3.18)           | .187 (4.75)           |

**NUT DETAIL**



**LOCKWASHER DETAIL**



INCHES (MM)

