

## Miniature PCB Relay OJS 10A/16A

- 1 pole 10/16A, 1 form A (NO)
- 10A rating with sensitive coil 200mW
- Small size (18.2 x 10.2 x 14.8mm)
- 4000Vrms coil to contact dielectric strength
- Product in accordance to IEC 62368-1









## Typical applications

Lihting, smart plug, power supply, appliances, industrial control.

Approvals
Will change to new certification No. TUV R50497672, UL E82292,
CQC21002289617

Technical data of approved types on request

Contact Data	
Contact arrangement	1 form A, 1 NO
Rated voltage	250VAC
Max. switching voltage	250VAC
Rated current	10A, 16A
Contact material	AgSnOlnO
Min. recommended contact load	100mA at 5VDC
Frequency of operation	360 ops./h
Operate/release time max.	15ms/4ms
Electrical endurance	
UL508	
HM, 10A, 250VAC, +85°C	50x10 <sup>3</sup> ops.
HE, 16A, 250VAC, +85°C	30x10 <sup>3</sup> ops.
IEC 61810-1	
8A, 250VAC res, +23°C	100x10 <sup>3</sup> ops.
Mechanical endurance, DC coil	10x10 <sup>6</sup> ops.

Coil Data		
Coil voltage range	5 to 48VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL	Class F	

Coil versions, DC coil, OJS-HM type

con received be con, ede thin type						
Coil	Rated	Operate	Release	Coil	Rated coil	
code	voltage	voltage	voltage	resistance	power	
	VDC	VDC	VDC	$\Omega \pm 10\%$	mW	
03	3	2.25	0.15	45	200	
05	5	3.75	0.25	125	200	
06	6	4.5	0.3	180	200	
09	9	6.75	0.45	405	200	
12	12	9	0.6	720	200	
24	24	18	1.2	2880	200	
48	48	36	2.4	11520	200	
A II 61					0000	

All figures are given for coil without pre-energization, at ambient temperature +23°C

Coil versions DC coil O.IS-HE type

Coll versions, DC coll, O35-nE type						
Coil	Rated	Operate	Release	Coil	Rated coil	
code	voltage	voltage	voltage	resistance	power	
	VDC	VDC	VDC	Ω±10%	mW	
03	3	2.25	0.15	20	450	
05	5	3.75	0.25	56	450	
06	6	4.5	0.3	80	450	
09	9	6.75	0.45	180	450	
12	12	9	0.6	320	450	
24	24	18	1.2	1280	450	
48	48	36	2.4	5120	450	

Insulation Data	
Initial dielectric strength	
between open contacts	750V <sub>rms</sub>
between contact and coil	4000V <sub>rms</sub>
Clearance/creepage	
between contact and coil	7mm / 11mm
Type of insulation	Reinforced insulation

#### **Other Data**

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at

	www.te.com/customersupport/ronssupportcenter
Ambient temperature	-40°C to +85°C
Category of environment	al protection
IEC 61810	RTII - flux proof
	RTIII - wash tight
Shock resistance (function	onal) 10g

Shock resistance (destructive) 100g Weight Approx. 5.8g Resistance to soldering heat THT


IEC 60068-2-20 RTII: 270°C/10s RTIII: 260°C/10s Packaging unit tray/100, Carton box/1000





## Miniature PCB Relay OJS 10A/16A (Continued)

#### **Dimensions**


#### OJS HM 10A Outline and PCB Layout









#### OJS HE 16A Outline and PCB Layout









# **Terminal assignment**Bottom view on solder pin

Bottom view on solder pins





## Miniature PCB Relay OJS 10A/16A (Continued)



Product code	Rating	Enclosure	Coil voltage	Coil power	Insulation	Part number	
OJS-SH-105HMF, 00000		Wash tight	5VDC	-		2071556-8	
OJS-SH-112HMF, 00000			12VDC			2071556-7	
OJS-SH-124HMF, 00000	104		24VDC	200mW		2071556-9	
OJS-SS-105HMF, 00000	10A	Flux proof	5VDC	20011100		2071556-6	
OJS-SS-112HMF, 00000	]		12VDC			2071556-4	
OJS-SS-124HMF, 00000	1			24VDC		Class F	2071556-5
OJS-SH-105HEF, 00000			5VDC		Class F	1-2071556-2	
OJS-SH-112HEF, 00000	- 16A	Wash tight	12VDC			2071556-3	
OJS-SH-124HEF, 00000			24VDC	450mW		1-2071556-0	
OJS-SS-105HEF, 00000			5VDC	43011100		1-2071556-1	
OJS-SS-112HEF, 00000		Flux proof	12VDC			2071556-1	
OJS-SS-124HEF, 00000			24VDC			2071556-2	

Other types on request.

This list represents the most common types and does not show all variants covered by this data sheet.

Datasheets and product data is subject to the

terms of the disclaimer and all chapters of

the 'Definitions' section, available at

http://relays.te.com/definitions