INDUCTORS

⊗TDK

Inductors for power circuits Wound ferrite VLBU series



VLBU9664100L type




FEATURES

- This is a power supply circuit for SMD inductors using low-loss ferrite materials.
- \bigcirc Large current and lower DCR were achieved by the connecting wire-less structure.
- O This is a narrow inductor for multiphase operation, such as Vcore regulators, Voltage Regulator Modules (VRMs), Point-of-Load, and memory power applications.
- Support in PMIC Evaluation Kits.
- VLBU series is satisfied high efficiency requirements for VR13 and VR14 applications.
- Operating temperature range: -40 to +125°C (including self-temperature rise)

APPLICATION

○ Servers, BTS, VRM, others

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

L		Measuring frequency	DC resistance		Rated current*		Part No.
					Isat	Itemp	
(µH)	Tolerance	(kHz)	(m Ω)typ.	Tolerance	(A)typ.	(A)typ.	
0.07	±20%	100	0.125	±10%	150	75	VLBU9664100LT-R07M
0.09	±15%	100	0.125	±10%	120	75	VLBU9664100LT-R09L
0.10	±15%	100	0.125	±10%	110	75	VLBU9664100LT-R10L
0.12	±15%	100	0.125	±10%	90	75	VLBU9664100LT-R12L
0.15	±15%	100	0.125	±10%	76	75	VLBU9664100LT-R15L
0.18	±15%	100	0.125	±10%	60	75	VLBU9664100LT-R18L

* Rated current: smaller value of either lsat or Itemp.

Isat: When based on the inductance change rate (20% below the nominal value, under an environment of 20°C)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Measurement equipment


Measurement item	Product No.	Manufacturer
L	IM3536	HIOKI
DC resistance	RM3545	HIOKI
Rated current Isat	3260+3265B	Wayne Kerr Electronics

* Equivalent measurement equipment may be used.




VLBU9664100L type

L FREQUENCY CHARACTERISTICS



Measurement equipment			
Product No.	Manufacturer		
4294A	Keysight Technologies		
* Equivalent measurement equipment may be used.			

■ INDUCTANCE VS. DC BIAS CHARACTERISTICS




* Equivalent measurement equipment may be used.


A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (2/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

VLBU9664100L type

SHAPE & DIMENSIONS








Dimensions in mm


PACKAGING STYLE



Dimensions in mm


RECOMMENDED LAND PATTERN

RECOMMENDED REFLOW PROFILE



Dimensions in mm

TAPE DIMENSIONS



Туре	А	В	К
VLBU9664100L	(6.6)	(9.8)	(10.2)


PACKAGE QUANTITY

Package quantity

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight
–40 to +125 °C	–40 to +125°C	2.6 g
* Operating temperature range includes self-temperature rise.		

** The storage temperature range is for after the assembly.



Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

20201001

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

 The storage period is within 6 months. Be sure to follow the stora less). If the storage period elapses, the soldering of the terminal electrod 				
 Do not use or store in locations where there are conditions such as 				
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature does not exceed 150°C. 	e difference between the solder temperature and chip temperature			
 Soldering corrections after mounting should be within the range of If overheated, a short circuit, performance deterioration, or lifespan 	-			
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.				
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set therma design.				
 Carefully lay out the coil for the circuit board design of the non-mag A malfunction may occur due to magnetic interference. 	netic shield type.			
○ Use a wrist band to discharge static electricity in your body through	the grounding wire.			
\bigcirc Do not expose the products to magnets or magnetic fields.				
\bigcirc Do not use for a purpose outside of the contents regulated in the definition of the contents regulated in the definition of the content	elivery specifications.			
ment, industrial robots) under a normal operation and use condition The products are not designed or warranted to meet the requirement ity require a more stringent level of safety or reliability, or whose fait person or property.	nent, personal equipment, office equipment, measurement equip-			
 (1) Aerospace/aviation equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (3) Medical equipment (4) Power-generation control equipment (5) Atomic energy-related equipment (6) Seabed equipment (7) Transportation control equipment When designing your equipment even for general-purpose application tection circuit/device or providing backup circuits in your equipment. 	 (8) Public information-processing equipment (9) Military equipment (10) Electric heating apparatus, burning equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (13) Other applications that are not considered general-purpose applications 			

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.