

# EURO PLUGTOP- 12vdc 6W



## TIGER PART: TP1133

### Features:

- Built in Over Current and Short Circuit Protections
- Universal 100-240vac input voltage
- Supplied with fixed EUROPEAN AC pins
- Level VI efficiency
- Approved to latest EN 62368-1 safety standard
- Dimensions just 43.6 x 40.9 x 22.9mm



The Tiger Power range of switch mode power supplies feature full safety approvals to latest 62368-1 standards and also level VI energy efficiency requirements. The TP1133 12vdc 0.5A amp model provides a reliable constant voltage output at up to 6 Watts continuous, suitable for a wide range of applications.

Part number (Black Case):	TP1133
Part number (White Case):	TP1133-W
AC pins:	Fixed European
Input voltage:	100-240vac (90-264vac max.)
Input frequency:	47 - 63Hz
Output voltage:	12vdc
Current:	0.5A
Power :	6 Watts
Protection:	Short Circuit, Over Current protection
Dimensions:	43.6 x 40.9 x 22.0mm
Weight:	150g
Standby Power Consumption :	0.1W max.
DC cord length:	1.5 metres
DC connector:	2.1 x 5.5 x 12mm (Female) Other options on request
Polarity:	+ve (positive) centre
Efficiency:	88%
Input current RMS Max.:	1.5A
Inrush Current at 230vac:	40A max.
Load regulation:	+ / - 5%
Safety approval:	62368-1 including UL (USA), CE and C-Tick.
M.T.B.F:	50,000 hours
Operating temperature:	0°C to + 40°C

### TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.