4P4C Modular Plug

multicomp PRO

RoHS Compliant



Specifications:

Current Rating
Voltage Rating
Maximum Contact Resistance
Minimum Insulator Resistance
Withstanding Voltage
Operating Temperature Range
Gender
No. of Ports
Contact Termination
No. of Ways


Material and finish:


Insulator Contact Plating : 1A AC/DC : 150V AC/DC : 20mΩ : 1,000MΩ : 500V AC for one minute : -40°C to +125°C : Plug : 1 : IDC / IDT : 4/4


: High Temperature Plastic

- : Phosphor Bronze
- : Gold Plated

Diagram







For flat cable

Part Number Table

Description	Part Number
Modular Plug, 4P4C, Flat	7001-4P4C

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

