## Toggle Switches



Well known for their quality and reliability, Bulgin's toggle switches are cost effective solutions to many existing applications. These switches offer features at an attractive price point often well below that of the existing competition.

- O Nylon and Metal switch variants
- Multiple Lever Options
- Ratings up to 20A, 250V ac 277V ac
- IP67 panel seal versions, supplied complete with gaskets (3900 Series – All Variants)
- O Single and double pole
- Choice of circuit options including 3 position and momentary
- O Mounting hole: 12.2mm diameter.
- Sealing accessories available
- Quick Connect, Solder, Screw and PCB Termination Options





# 3900 Metal Toggle Switches 16A 250Vac - IP67 Sealed Versions





### **Key Features**

- Metal toggle switches
- Ratings up to 20A, 277V ac
- Single and double pole
- Choice of circuits including 3 position and momentary
- Sealed version supplied complete with gaskets
- O Panel seal version to IP67
- 0 6.3mm terminals
- O Guard option

Terminal	Function		Actuator	Body	Options
C 10.5 6.3 x 0.8  S 10.5 Screw & Clamp	Single Pole  3900 ON - OFF  3901 ON - OFF (momentary ON)  1	Double Pole  3950 ON - OFF (momentary ON)  1	Metal toggle finish is nickel plate  Metal toggle finish is nickel plate   Metal toggle finish is nickel plate   Metal toggle finish is nickel plate   Metal toggle finish is nickel plate   Metal toggle finish is nickel plate	A Single pole Thread: 15/32* x 32TPI Keyway  A Double pole, without barrier Thread: 15/32* x 32TPI Keyway  Tr.5 10.0 30.6  B Double pole, with barrier Thread: 15/32* x 32TPI Keyway  Tr.5 10.0 30.6  F Panel sealed, double pole, with terminal barrier Thread: 15/32* x 32TPI Keyway  Tr.5 10.0 30.6  G Panel sealed, double pole, without terminal barrier Thread: 15/32* x 32TPI Keyway  Tr.5 10.0 31.1  Switches with F toggles have double pole bodies, regardless of circuit  G Panel sealed, double pole, without terminal barrier Thread: 15/32* x 32TPI Keyway  Tr.5 10.0 31.1  Switches with F toggles have double pole bodies, regardless of circuit	Neck Seal M539 Actuator is visible  Cover M1080  Covers have internal nylon nuts M1080-2  Covers have internal metal hex nuts  Fixing nuts Nickel plated brass are supplied  14.0  15.0  15.0  14.0  14.0  15.0  15.0  17.0  18.0  19.0  1



#### **Approvals and specifications**

W UL/CSA Ratings 3901, 3902, 3920, 3921, 3922 16A, 277Vac 1 HP, 250Vac

**91 ©** 7A, 72Vdc 14A, 36Vdc

> 3910, 3901, 3952, 3960, 3961, 3970, 3971, 3972 16A, 277Vac 1 HP, 250Vac 1/2 HP, 125Vac 7A, 72Vdc 14A, 36Vdc

3900, 3950 20A, 277Vac 1 HP, 250Vac 1/2 HP, 125Vac 7A, 72Vdc 14A, 36Vdc

ENEC Ratings 3900, 3901, 3902, 3950, 3952, 3960, 3961 16(4)A 250Vac

3910, 3911, 3920, 3921, 3922, 3951, 3970, 3972 10 4)A 250Vac


Approvals and ratings vary with function. 3mm contact gap except where marked  $\boldsymbol{\mu}.$ 

\* CSA approval for A and B bodies only


#### **Dimensions** mm) \* Indicates ON position (for ON - OFF switches)

#### Single pole

(C terminals shown)








#### Double pole

(C terminals shown with barrier)









#### Toggle Switch - sealed version

BE and BF types



**Guard TG1-RED** 



#### **Examples**







C3920BA - - -



C3950BF - - -



C3972BB - - -





#### **Key Features**

- Nylon toggle switches
- Ratings up to 20A, 250V ac
- O Single and double pole
- Wide choice of terminals
- Choice of circuit options including 3 position
- Flat & round actuator options

#### **Approvals and specifications**

16(4)A 250Vac T85

UL 20A 250Vac Non Ind (Single pole)
UL 16A 250Vac Non Ind (Double pole)
UL CSA (2 pos types) 250Vac 1hp, 125Vac 1/2hp
UL CSA (3 pos types) 250Vac 1/2hp, 125Vac 1/4hp
CSA 16A 250Vac Non Ind
UL 85°C, file E45221, CSA file LR10990
UL and CSA N/A on momentary types

Selective "A, B, C" and "OFF, A, A+B" circuits at 5 amp also available. 3mm contact gap except where marked  $\mu$ .

Terminal	Function		Actuator	Body	Options
C	Single Pole  1700 ON - OFF	Double Pole  1750 ON - OFF	H 16.4	Single pole  Thread: 15/32" x 32TPI  Keyway  10.0  12.2	Neck Seal M539  Material - Nitrile (H & R Actuators) Actuator visible  Cover M1080  Material - EPDM (R Actuator only)
K 2.0 1 9.1  T 7.0	1710 μ ON - ON 1720 μ ON - OFF - ON	1760 μ ON-ON THE THE	R 13.8 •	Double Pole Thread: 15/32" x 32TPI Keyway  15.5-0.1  15-0.1  15-0.1  Panel hole (all types)	Cover M531  Material - PVC (R Actuator only)  Covers have internal nylon nuts  Fixing nuts (Standard is M506 & T92)
X 4.0 ★ ¶9.1	1721 μ ON - OFF - ON μ (momentary 1 side) 1722 ON - OFF - ON μ (momentary 2 sides)		The switch is on between centre terminals (2 & 5) and the terminals over which the lever is positioned.	Panel thickness (Max) Both nuts - 3.5mm Less backnut - 6.5mm	M506 Hex nylon  3.0 (M505)  T92 Knurled brass - 16.0 2.6  M279 Knurled nylon 16.2 16.2  Plate P236 Plate SP or DP



**Dimensions** mm) \* Indicates ON position (for ON - OFF switches)

#### Single pole

(C terminals shown)







Optional F00232PAAA plate SP or DP

#### Double pole

(C terminals shown)





Without barrier

With barrier 1A 2A 3A

#### **Examples**









C1700R - -

C1700H - -

C1760R - -

C1750H - -