1500 Standard & 1300 High Inrush Switches 150A to EN61058-1 and 16A 250Vac





Key Features

O Non-illuminated

○ Choice of switching

circuits including 3

○ Choice of bezel styles

150A inrush

position

- O Standard rocker switch O Matching indicator
 - Single pole
 - O Splash resistant option
 - O DC LED Illumination Avaliable for "P" Rocker O Panel cut out 'A' style:
 - 27.3 x 12.3mm
- Choice of panel cut outs

Approvals and specifications

- « 1500 Series 16(4)A 250Vac T125
- ₩ UL CSA 16A Non Ind 250Vac, (2 posn) 250Vac 1hp, 125Vac 1/2hp, (3 posn) 250Vac 1/2hp, 125Vac 1/4hp 1330 36Vdc 14A 1350 72 Vdc 7A 1500 & 1510 14 Vdc 10A UL 85°C, file E45221, CSA file LR10990

In house test: 10A 24Vdc-Indicative rating only

1300 series 16(6)A 250Vac T125 5E4 (50,000 Ops.) 150A Inrush to EN61058-1

Terminal	Function	Rocker	Body	Finish	Body Colour
C	Standard 1500 ON - OFF 1501	Softline Matt	Panel cut-out Bezel Cut-outs must be punched in the direction of insertion	M Matt	B Black
6.3 x 0.8 H	HP rating N/A ON - OFF (momentary ON) 1502 HP rating N/A ON - OFF (momentary OFF)	B Splash resistant (with Arcshield) Matt	A 27.3 12.2/12.3 Gloss or Matt	G Gloss	R Red
4.8 × 0.8*	1510 μ HP rating N/A ON - ON 1511 μ	Slotted (for custom Adaptors) not momentary	B 30.0 30.1 11.0/11.1 Matt only	Applies to both Rocker & Body	W White
K	HP rating N/A ON - ON (momentary 1 side) 1520 μ 125V & 250V 1/2 HP H terminal rated T100 only ON - OFF - ON	Curved Matt or gloss	L 30.0 30.1 11.0/11.1 Matt only		
2.8 × 0.8*	1521 μ HP rating N/A H terminal rated T100 only ON - OFF - ON (momentary 1 side)	Splash resistant (with Arcshield) Matt	Q R1.6 30.2		
Ø2.1	1522 μ HP rating N/A H terminal rated T100 only ON - OFF - ON (momentary 2 sides) 0430	Two colour Matt ON - OFF only (not momentary)	11.5/11.6 ⊫14.01 Gloss or matt		
Solder	HP rating N/A H terminal rated T100 only 1484 In-house tested to 10(3)A 250Vac 3 position selective	Flat lens Gloss (0430 only)	R 14.0/14.1 F 17.0 F		
Ø2.1 • • Right angle "T" solder terminal	1487 In-house tested to 10(3)A 250Vac 3 position selective	Softline lens Matt (0430 only) as F but with raised profile	T 11.5/11.6 Matt only ■ 1.6 11.6/11.6 ■ 1.6 ■ 1.6		
	High Inrush 1300 on - Off				



UL CSA 20A 250Vac 1hp, 125Vac 1/2hp UL 85°C, file E45221, CSA file LR10990

In house test: 20A 24Vdc-Indicative rating only

The 1500 & 1300 switch range are capable of reaching in excess of 300K cycles

BioCote antimicrobial additive. Independently verified to ISO22196:2007.

3mm contact gap except if marked µ.

Dimensions

-9.2 Panel thickness A,Q 0.75 to 3.3mm L,B,T 0.75 to 2.5mm R 0.75 to 3.0mm

* For cut-out details on momentary switches call sales

Splash Resistance

1500 W and B splash resistant options Feather edge seals and a close fitting collar protect current carrying parts from moisture. B option has Hytrel collar/seals for enhanced protection.



1300 High inrush, positive break switching The 1300 series mechanism ensures contact welds formed at switch-on are positively separated by the plunger tube acting directly on the step in the moving contact.

Rocker Colour	Lamp Voltage	Insert Colour	Legend	Legend Colour	Options
Un-Lit	Blank	 Blank	 Blank	Blank	Finish Matt is standard. Colour Call sales for custom colours. A full range is available for large
Black R Red	2 125V Neon	R Red	602A	B Black	orders. Legend printing Select from the examples or call sales for custom legends. Lamp voltage Call sales for details.
W White	3 250V Neon 7 12V Filament	W White		White	Blanking plates A0434 Dummy units to fill unused panel holes. Protective cover Snaps on to A, L, Q or T bodies (add G after body code in cat no.), this reduces panel thickness by 1mm.
Lit	8 24Vdc Filament				
A Amber C Clear					Panel sealing washer W46 is available for the same body sizes, this reduces panel thickness by a further 0.8mm. Covers are not suitable for momentary types.
G Green					For all options call sales.
R Red	Examples				
		1			I
				고 C1510AL 고 C1520AL 귷 T1510AL 귷 T1520AL	

5500 Lit Rocker Series

10A 250Vac



O Standard rocker switch

○ Single pole

O Splash resistant option

O Panel cut out 'A' style:

- O Illuminated
- Choice of switching circuits
- Choice of bezel styles
- Choice of panel cut outs
- O Matching indicator




bulgin

- 16(4)A 250Vac T85
 10(3)A 250Vac T100, (12A 250Vac T125 for P rocker only)
- **N** UL CSA 15A 250Vac, CSA 16A Non Ind 250Vac UL CSA 250Vac 1hp, 125Vac 1/2hp UL 85°C, file E45221, CSA file LR10990

µ contact gap.

For Twin units repeat the order details for both the left and right sides.





Dimensions

 Panel thickness

 A,Q
 0.75 to 3.3mm

 L,B,T
 0.75 to 2.5mm

 R
 0.75 to 3.0mm



Twin units

Two single switches or a switch and an indicator light can be assembled side by side in one double pole body. For 5500 range panel cut-out details (L, B and T) call sales.



Terminal spacing -Poles 10.8 between centres (twin units) For twin units the first set of order format details refer to the left hand unit, when looking at the front of the assembly. (This has terminal numbers 1, 2 & 3)

Lamp Voltage	Legend	Legend Colour	Options
Blank	Blank	Blank	Finish Matt is standard. Colour Call factory for custom colours.
2 125V Neon	602A	B Black	A full range is available for large orders. Legend printing Select from the examples or call factory for custom legends. Lamp voltage
3 250V Neon		W	Call factory for details. Blanking plate A0434 (SP) A0494 (DP) Dummy units to fill unused panel holes. Protective cover Snaps on to A, L, Q or T bodies (add G after body in cat no.), this reduces panel thickness
5 12Vdc LED (P Rocker) IF = 20-30mA			by 1.00mm.
6 24Vdc LED (P Rocker) IF = 20-30mA			
7 12V Filament			Panel sealing washers W46 (Single Pole) and W42 (Double Pole) are available for these body types, this reduces panel thickness by 2mm.
8 24Vdc Filament			For all options call the factory.

Examples













C5503AL - - -

🗉 C5500AL - - -

🗉 C5503PL - - -

C5503A/C5430AL

C5503A/C5503AL

C5503P/C5503PL

1500 Twin Units Switches and Indicators

16A 250Vac



Key Features

terminals

O Twin unit rocker switch

O Push-on, solder and PCB

O Choice of bezel styles

Matching indicatorSingle pole switches

O Choice of panel cut outs

- Choice of switching circuits including 3 position
- Splash resistant option
 Panel cut out 'A' style: 27.2 x 22.3mm
- Approvals and Specifications

bulgin

🏽 16(4)A 250Vac T125

UL CSA 16A 250Vac
 UL CSA (2 posn) 250Vac 1hp, 125Vac
 1/2hp, (3 posn) 250 Vac
 1/2hp, 125Vac 1/4hp
 UL 85°C, file E45221, CSA file LR10990

For versions with High Inrush or for 50,000 operations, 3mm contact gap except where marked µ.

Terminal	Function	Rocker	Body	Finish	Body Colour	Rocker Colour	
C	Approvals & ratings vary with function ON OFF Switches - ON when pressed over terminal 1 or 4 $1 \frac{1}{2} \frac{1}{2} \frac{1}{2}$	A Softline (Matt only)	Panel Cut - outs Bezel $A \begin{bmatrix} 1 \\ 27.2 \\ 27.3 \end{bmatrix} \begin{bmatrix} 30.2 \\ 30.2 \end{bmatrix}$	M Matt	B Black	Un-Lit B Black	
6.3×0.8	1500 ••• •••	B Softline (Matt only)	B	G Gloss	W White	R Red	
4.8 x 0.8	1510 µ •••••	Softline (Matt only)	$L \begin{bmatrix} 30.0\\ 30.1\\ 30.1 \end{bmatrix}^{R1.0} \begin{bmatrix} 32.0\\ 32.0 \end{bmatrix}$	Applies to both Rocker & Body		White	
02.1 Solder	1520 µ ••••••••••••••••••••••••••••••••••••	Softline (Matt only)	Q 28.2 28.2 28.2 28.3 R1.6 R1.6 R1.6 R1.6 R1.6 R1.6 R1.6 R1.6			Lit A Amber	
	Indicator	Softline (Matt only)	R R R R R R R R R R			Clear	
			23.0/25.4 Matt only			G Green	
			T 28.2 28.3 22.3/22.4 Matt only 30.2 4 Matt only 30.2			R Red	



Dimensions

 A,Q
 0.75 to 3.3mm

 L,B,T
 0.75 to 2.5mm


 R
 0.75 to 3.0mm



Call sales for terminal spacing details

Twin units

Two single switches or a switch and an indicator light can be assembled side by side in one double pole body.



For twin units the first set of order format details refer to the left hand unit, when looking at the front of the assembly. (This has terminal numbers 1, 2 & 3)

Splash Resistant



Feather edge seals and a close fitting collar protect current carrying parts from moisture.

B option has Hytrel collar/ seals for enhanced protection.

Insert Colour	Lamp Voltage	Legend	Legend Colour	Options
 Blank		 Blank	Blank	Finish Matt is standard. Colour Call factory for custom colours. A full range is available for large orders.
R Red	2 125V Neon	602A	B Black	Legend printing Select from the examples or call factory for custom legends. Lamp voltage
White	3 250V Neon		W	Call factory for details.
	5 12Vdc LED (P Rocker)			
	6 24Vdc LED (P Rocker)			
	7 12V Filament			
	8 24Vdc Filament			

Examples













□ C1500A/C1500AL

C1500A/C0430AL

C1500X/C1500XL

C1520A/C1510AL

C1500A/C1520AL

C0430A/C0430AL