Hook-up Wire



RoHS Compliant



Features

- · Available in Tin Copper, Bare Copper, or Topcoat
- PVC (Polyvinylchloride) Insulation, 105°C, 600V: UL 1032 1000V
- MTW AWM 1015, 1230, 1332, 1335 VW-1 FT-1 TEW
- Exceptions: MTW only on stranded 22 AWG or larger

Specification Table

Part Number	Colour	Construction	Insulation	Insulation (Inches)	Nom. OD (Inches)	Temperature	Voltage	Product Type
24-16040	Black	18 (16x30) TC	PVC	0.03	0.106	105°C	600	1015 / 1230 / 1335 / 1032
24-16041	Brown							
24-16042	Red							
24-16044	Yellow							
24-16045	Green							
24-16046	Blue							
24-16049	White							

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

