## **Data Sheet**



## **CBN** cutter

Long-lasting high precision CBN endmill for mold steel. Applicable for working material Mold Steel HRC 50-68 finishing machining. Radius tolerance:  $\pm 0.005$ mm; Flute diameter tolerance:  $\pm 0/0.01$ mm





## **Cutter specification**

• P/N: **DK02003ZO** 

• Specification: D2R0.1xFL8-CBN

• Shank diameter: 6mm

• Working material: Mold steel HRC 50-68

• Radius tolerance: ±0.005mm

• Flute diameter tolerance: +0/ -0.01mm

• Total length: 50mm

## **Recommend cutting parameter**

Working material: Mold steelMachining type: Fine finishing

• Rpm: 16000

• Feed rate: 800mm/min

• Cutting depth (Ap): 0.01mm

• Cutting width (Ae): 0.8mm