Switched Filtered Power Entry Modules with Double Fuse





RoHS Compliant

Characteristics

Part Number	PELB1086	PELB1087	PELB1088	PELB1089	
Voltage Rating	115/250V AC				
Current Rating A. @ 115 V AC B. @ 250 V AC	1A RMS Max. 1A RMS Max.	3A RMS Max. 3A RMS Max.	6A RMS Max. 6A RMS Max.	10A RMS Max. 10A RMS Max.	
Operating Frequency	50/60Hz				
Leakage Current A. @ 115 V AC/60Hz B. @ 250 V AC/50Hz	Each Line to Ground 0.3mA Max. 0.6mA Max.				
Hipot Rating A. Line to Ground B. Line to Line	(For one minute) 2250V AC 500V DC				
Insulation Resistance	50mΩ at 500V DC any input or output to Ground				
Temperature Range	-25°C to +85°C				

Electrical Schematic

PELB1086	PELB1087	PELB1088	PELB1089			
Fuse SWI R CX CX CX CX D A E Fuse D						
L:2×6.5mH	L:2×4.0mH	L:2×1.8mH	-			
C×: 0.1µF(X2)						
Cy: 3300pF(Y2) * 2						
R: 1MΩ						





Switched Filtered Power Entry Modules with Double Fuse




Safety Compliance


CE : 2011NT0616551 TUV : B0899310001 UL : E471748

Dimension Limit	Tolerance	
0 - 10	±0.3	
10 - 100	±0.5	
100 - 150	±0.8	
150 - 200	1.0	

Physical Dimensions



SUGGESTED PANEL CUTOUT (MOUNTING FROM FRONT)



Part Number Table

Description	Part Number
Switched Filtered IEC Inlet C14 with Double Fuse, 250V AC, 1A	PELB1086
Switched Filtered IEC Inlet C14 with Double Fuse, 250V AC, 3A	PELB1087
Switched Filtered IEC Inlet C14 with Double Fuse, 250V AC, 6A	PELB1088
Switched Filtered IEC Inlet C14 with Double Fuse, 250V AC, 10A	PELB1089

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

