K10D004NCH

Cam stepping switch, 1 pole, without off position, 60° switching angle, 10 A, for Ø 16 or 22 mm



Main

| Range of product | Harmony K |
|---|---|
| Product or component type | Complete cam switch |
| Component name | K10 |
| [Ith] conventional free air thermal current | 10 A |
| Product mounting | Front mounting |
| Fixing mode | Ø 16 or 22 mm hole |
| Cam switch head type | With front plate 30 x 30 mm |
| Type of operator | Black handle |
| Rotary handle padlocking | Without |
| Presentation of legend | With metallic legend, 1 - 2 - 3 - 4 black marking |
| Cam switch function | Stepping switch |
| Return | Without |
| Off position | Without Off position |
| Poles description | 1P |
| Switching positions | Right: 270° - 330° - 30° - 90° |
| IP degree of protection | Contact block IP20 Operating head IP65 IEC 60529 |

Complementary

| Complementary | | |
|--|--|--|
| Number of steps | 4 | |
| Switching angle | 60 ° | |
| [Ui] rated insulation voltage | 440 V 3)IEC 60947-1 | |
| Rated operational power in W | 370 W AC-23A, 110/120 V 1 phase 750 W AC-23A, 220/240 V 1 phase | |
| Rated power in hp | 0.33 Hp 110/120 V AC, 1 phase 0.75 hp 220/240 V AC, 1 phase | |
| [le] rated operational current AC | 10 A 400 V AC-1 10 A 400 V AC-21A 3 A 240 V AC-15 6 A 120 V AC-15 | |
| [le] rated operational current DC | 10 A 24 V resistive 0.3 A 220 V resistive 0.7 A 110 V resistive | |
| Electrical durability | 100000000 cycles | |
| Short-circuit protection | 10 A cartridge fuse, type gG | |
| [Uimp] rated impulse withstand voltage | 4 kV IEC 60947-1 | |
| Contact operation | Slow-break | |
| Electrical connection | Captive screw clamp terminals 2 x 1.5 mm ² | |
| Mechanical durability | 1000000 cycles | |
| CAD overall width | 1.18 in (30 mm) | |
| CAD overall height | 1.18 in (30 mm) | |
| CAD overall depth | 3.46 in (88 mm) | |
| Net Weight | 0.10 lb(US) (0.045 kg) | |

Environment

| Standards | CENELEC EN 50013 EN/IEC 60947-3 EN/IEC 60947-5-1 |
|---------------------------------------|--|
| Product certifications | CULus |
| Protective treatment | TC |
| Ambient air temperature for operation | -4131 °F (-2055 °C) |
| Ambient air temperature for storage | -40158 °F (-4070 °C) |
| Electrical shock protection class | Class II IEC 60536 |

Ordering and shipping details

| Category | 21446 - 9003 K CAM SWITCHES |
|-----------------------|-----------------------------|
| Discount Schedule | CS1 |
| GTIN | 00785901639077 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.13 lb(US) (0.06 kg) |
| Returnability | No |
| Country of origin | AT |
| | |

Packing Units

| racking office | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.57 in (4 cm) |
| Package 1 width | 1.61 in (4.1 cm) |
| Package 1 Length | 4.13 in (10.5 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 65 |
| Package 2 Weight | 9.54 lb(US) (4.326 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |
| | |

Offer Sustainability

| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
|----------------------------|--|
| REACh Regulation | ☑ REACh Declaration |
| REACh free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EPEU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | ₫Yes |
| China RoHS Regulation | ☑ China RoHS Declaration |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty


| Warranty | 18 months |
|----------|-----------|

Product data sheet Dimensions Drawings

K10D004NCH

Cam Switch

Front Mounting by Ø16 mm/0.63 in. or Ø 22 mm/0.87 in. hole




- a 63 mm/2.48 in.
- e support panel thickness: 0.5 mm to 5 mm/0.02 in. to 0.2 in.

Product data sheet Mounting and Clearance

K10D004NCH

Cam Switch


Ø 16 mm/0.63 in. and Ø 22 mm/0.87 in. Panel Cut-outs



Product data sheet Technical Description

K10D004NCH

Link Positions (Factory Mounted)



Marking



Angular Position of Switch



Switching Program



Convention Used for Switching Program Representation

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

