

## Power Versa-Lock | Power Versa-Lock 5.0

TE Internal #: 2325349-1 Power Versa-Lock 5.0, Rectangular Connector Seals, Gang Wire Seal, Accepts Wire Insulation Diameter Range 2.45 – 3.6 mm [.097 – .142 in], Wire-to-Wire

### View on TE.com >





### Connector Seal Type: Gang Wire Seal

Accepts Wire Insulation Diameter Range: 2.45 – 3.6 mm [.097 – .142 in]

Connector System: Wire-to-Wire

Number of Positions: 1

Sealable: Yes

## Features

### **Product Type Features**

Accessory Color	Blue
Product Type	Accessory
Connector Seal Type	Gang Wire Seal
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Configuration Features	
Number of Positions	1
Body Features	
Material	Silicone Rubber
Seal Color	Blue
Seal Material	Silicone Rubber
Dimensions	
Accepts Wire Insulation Diameter Range	2.45 – 3.6 mm[.097 – .142 in]
Usage Conditions	
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
Operation/Application	



**C** For support call+1 800 522 6752

## 2325349-1

Power Versa-Lock 5.0, Rectangular Connector Seals, Gang Wire Seal, Accepts Wire Insulation Diameter Range 2.45 – 3.6 mm [.097 – .142 in], Wire-to-Wire



For Use With	Power Versa-Lock Sealed Connectors
Circuit Application	Power & Signal
Other	
Comment	IP67

## Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# **Compatible Parts**





## 2325349-1

Power Versa-Lock 5.0, Rectangular Connector Seals, Gang Wire Seal, Accepts Wire Insulation Diameter Range 2.45 – 3.6 mm [.097 – .142 in], Wire-to-Wire




# Also in the Series | Power Versa-Lock 5.0










# Customers Also Bought





## 2325349-1

Power Versa-Lock 5.0, Rectangular Connector Seals, Gang Wire Seal, Accepts Wire Insulation Diameter Range 2.45 – 3.6 mm [.097 – .142 in], Wire-to-Wire



## Documents

CAD Files 3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2325349-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2325349-1\_A.3d\_igs.zip

English

Customer View Model ENG\_CVM\_CVM\_2325349-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications Engineering Report

English