

DIN-Signal coax f, solder/crimp, 500hm



Part number	09 03 000 6261
Specification	DIN-Signal coax f, solder/crimp, 500hm
HARTING eCatalogue	https://b2b.harting.com/09030006261

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Coaxial contact
Description of the contact	Angled
Contacts for	DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5 DIN 41612 Bauform M 0+2 har-modular [®] M module, male, angled har-modular [®] M module, male, straight

Version

Termination method	Solder/crimp termination
Gender	Female contact for male connectors
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Impedance	50 Ω	
-----------	------	--

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Commercial data

Packaging size	100
Net weight	33.64 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors