

10A, 45V Trench Schottky Rectifier

FEATURES

- Patented Trench Schottky technology
- Excellent high temperature stability
- Low power loss, high efficiency
- High forward surge capability
- Compliant RoHS
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- On-board DC/DC converter

MECHANICAL DATA

- Case: ITO-220AB
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Mounting torque: 0.56 N·m maximum
- Polarity: As marked
- Weight: 1.72g (approximately)


KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	2 x 5	А		
V _{RRM}	45	V		
I _{FSM}	110	А		
T _{J MAX}	150	°C		
Package	ITO-220AB			
Configuration	Dual dies			



OHS HALOGEN







ABSOLUTE MAXIMUM RATING	$T_{A} = 25^{\circ}C$	unless otherwis	e noted)	
PARAMETER		SYMBOL	TSF10H45C	UNIT
Marking code on the device			TSF10H45C	
Repetitive peak reverse voltage		V _{RRM}	45	V
Reverse voltage, total rms value		V _{R(RMS)}	31	V
Forward current	per device	1	10	А
	per diode	I _F	5	Α
Surge peak forward current single half sine- wave superimposed on rated load per diode	t = 8.3ms	I _{FSM}	110	А
	t = 1.0ms		380	Α
Junction temperature		TJ	-55 to +150	°C
Storage temperature		T _{STG}	-55 to +150	°C





THERMAL PERFORMANCE			
PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-lead thermal resistance per diode	R _{ejl}	4.1	°C/W
Junction-to-ambient thermal resistance per diode	R _{eja}	15.6	°C/W
Junction-to-case thermal resistance per diode	R _{eJC}	4.2	°C/W

Thermal Performance Note: Mounted on Heat sink with 2" x 3" x 0.25" Al-Plate.

ELECTRICAL SPECIFICATIONS ($T_A = 25^{\circ}C$ unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
Forward voltage per diode ⁽¹⁾	$I_F = 2.5A, T_J = 25^{\circ}C$	V _F	0.42	-	V
	$I_F = 5.0A, T_J = 25^{\circ}C$		0.47	0.58	V
	$I_F = 2.5A, T_J = 125^{\circ}C$		0.31	-	V
	$I_F = 5.0A, T_J = 125^{\circ}C$		0.39	0.46	V
Reverse current @ rated V _R per diode ⁽²⁾	$T_J = 25^{\circ}C$	I _R	-	20	μA
	T _J = 125°C		-	15	mA
Junction capacitance per diode	$1 MHz, V_R = 4.0 V$	CJ	610	-	pF

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION		
ORDERING CODE	PACKAGE	PACKING
TSF10H45C	ITO-220AB	50 / Tube



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$




Fig.1 Forward Current Derating Curve







Fig.2 Typical Junction Capacitance










Fig.5 Typical Transient Thermal Impedance



PACKAGE OUTLINE DIMENSIONS





DIM.	Unit	(mm)	Unit	(inch)
	Min.	Max.	Min.	Max.
A	4.30	4.70	0.169	0.185
A2	2.30	2.96	0.091	0.117
b	0.50	0.90	0.020	0.035
b1	-	1.80	-	0.071
b2	0.95	1.45	0.037	0.057
с	0.46	0.76	0.018	0.030
c2	2.50	3.16	0.098	0.124
D	14.80	15.50	0.583	0.610
D1	2.40	3.20	0.094	0.126
D2	6.30	6.90	0.248	0.272
E	9.60	10.30	0.378	0.406
е	2.41	2.67	0.095	0.105
L	12.60	13.80	0.496	0.543
L4	-	4.10	-	0.161
Р	3.00	3.40	0.118	0.134

MARKING DIAGRAM



= Marking Code
= Green Compound
= Date Code
= Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.