

DIN-Signal high current m, 20A crimp



Part number	09 03 000 6114
Specification	DIN-Signal high current m, 20A crimp
HARTING eCatalogue	https://b2b.harting.com/09030006114

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Crimp contact
Contacts for	DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5 DIN 41612 Bauform M 0+2 har-modular [®] M module, male, angled har-modular [®] M module, male, straight
Version	
Gender	Male contact for male connectors
Manufacturing process	Turned contacts
Performance level	1
Technical characteristics	
Conductor cross-section	4 mm ²
Conductor cross-section	AWG 12
Operating current	≤20 A
Material properties	
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight

ELV status compliant with exemption
Page 1 / 2 | Creation date 2020-08-21 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to
the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality,
conformity with applicable laws and directives, as well as for the electrical safety in the particular application.
HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany

Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	DIN 41626
Commercial data	
	400
Packaging size	100
Net weight	1.96 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors