TE Internal #: T4061110003-003

M8/M12 Cable Assemblies, Sensor/Actuator, 3 Positions, A M8

/M12 Cable Assembly Keying, Plug, M8 Pigtail, Cable Assembly

Length 1500 mm

View on TE.com >



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 MALE STRAIGHT SINGLE ENDED CABLE ASSY











M8/M12 Application Type: Sensor/Actuator

Number of M8/M12 Cable Assembly Positions: 3

M8/M12 Cable Assembly Keying: A

M8/M12 Cable Assembly Connector Type: Plug

M8/M12 Cable Assembly Type: M8 Pigtail

All M8 MALE STRAIGHT SINGLE ENDED CABLE ASSY (56)

Features

Product Type Features

LED	Without
Cable Type	PVC
Product Type	Cable Assembly
Assembly Type	Pigtail
M8/M12 Cable Assembly Connector Type	Plug
M8/M12 Cable Assembly Type	M8 Pigtail
M8/M12 Cable Assembly Shielded	Yes
Configuration Features	
Number of M8/M12 Cable Assembly Positions	3

M8/M12 Cable Assembly Keying

M8/M12 Cable Assembly Configuration Single Ended

Mechanical Attachment

Screw & Hole Thread Size M8

Α



Housing Features

M8/M12 Cable Assembly Housing Material	PA66+25GF
Dimensions	
Cable Assembly Length	1500 mm
Operation/Application	
M8/M12 Application Type	Sensor/Actuator

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Pb (1.9% in Pb-Alloy in Copper) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts







Customers Also Bought



TE Part #1-2273047-4 M12 A-CODE FEMALE STRAIGHT PIGTAIL



TE Part #1-2273101-4 M12 A-CODE FEMALE R/A PIGTAIL
















Documents

Product Drawings

M8 CABLE ST M 1.5M 3POS PVC CABLE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4061110003-003_A.2d_dxf.zip



English

Customer View Model

ENG_CVM_CVM_T4061110003-003_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4061110003-003_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English