TE Internal #: T4161110004-003


M8/M12 Cable Assemblies, Sensor/Actuator, 4 Positions, A M8 /M12 Cable Assembly Keying, Plug, M12 Pigtail, Straight, Cable

Assembly Length 1500 mm

View on TE.com >



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-CODE MALE STRT SINGLE ENDED CABLE



M8/M12 Application Type: Sensor/Actuator

Number of M8/M12 Cable Assembly Positions: 4

M8/M12 Cable Assembly Keying: A

M8/M12 Cable Assembly Connector Type: **Plug** M8/M12 Cable Assembly Type: **M12 Pigtail** 

All M12 A-CODE MALE STRT SINGLE ENDED CABLE (139)

# Features

### **Product Type Features**

Troduct Type reduces	
LED	Without
Cable Type	PVC
Product Type	Cable Assembly
Assembly Type	Pigtail
M8/M12 Cable Assembly Connector Type	Plug
M8/M12 Cable Assembly Type	M12 Pigtail
M8/M12 Cable Assembly Shielded	Yes
Configuration Features	
Number of M8/M12 Cable Assembly Positions	4
M8/M12 Cable Assembly Keying	A
M8/M12 Cable Assembly Configuration	Single Ended
Electrical Characteristics	

250 VDC

Operating Voltage



## **Body Features**

Connector Color	Blue
Cable Exit Angle	Straight
Environmental Protection	With
Insulation Material	PVC
Conductor Material	Copper Alloy
Cable Jacket Color	Black
Contact Features	
Contact Current Rating	4 A
Mechanical Attachment	
Screw & Hole Thread Size	M12
M8/M12 Cable Assembly Mounting Angle	Straight
Housing Features	
M8/M12 Cable Assembly Housing Material	GF Nylon
Dimensions	
Wire Size	22 AWG
Cable Assembly Length	1500 mm
Operation/Application	
M8/M12 Application Type	Sensor/Actuator
Packaging Features	
Packaging Method	Bag
Other	

# **Product Compliance**

Field Serviceable

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020
	(209)
	Candidate List Declared Against: JAN 2020
	(205)

Yes



SVHC > Threshold:

Pb (1.9% in Pb-Alloy in Copper)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

# Compatible Parts



# **Customers Also Bought**





















#### **Documents**

#### **Product Drawings**

RPC-M12-MS-4CON-PVC-1.5SH

English

#### **CAD Files**

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_T4161110004-003\_A.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_T4161110004-003\_A.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_T4161110004-003\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

### Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

### **Product Specifications**

**Application Specification** 

English