


Part Number: 00000239

Type	Size	Rating	Description
Incandescent	11x38	12V 5W	Festoon Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			
	Min.	Nom.	Max.	Min.	Nom.	Max.	
13.5	333	370	407	40	50	60	

Notes:

- 1 **Base Type** SV8.5-9
- 2 **Filament Shape** Single coil
- 3 **Lamp Marking** E marked with 12V 5W
- 4 **Environmental** RoHS & REACH SVHC compliant