

CLAMPING EQUIPMENT SPANNFIX COMBINATIONS

9-250 **BERNSTEIN SPANNFIX-VARIO** assembly vice

5 piece set
with interchangeable screw-on work mounts
Weight: 2.000 kg

Description of individual components:

9-251 **Universal clamp mounting ball joint base**
for screwing onto work benches with a max. table thickness
of 80 mm
Weight: 0.950 kg

9-252 **Screw-on mounting vice**
Technical data: Clamping pressure 150 kp
Clamping capacity 70 mm
Clamping depth 38 mm
Jaw width 50 mm
Jaws (interchangeable) plastic
Weight: 0.560 kg

9-253 **Circuit board holder**
adjustable from 25 mm to 270 mm clamping capacity, can be
extended as required at any time, correct setting by adjusting
the centre position, protected against contact voltages, firm
clamping of the printed circuit by built-in resilience in the
locating arms, height of locating arms 70 mm.
Weight: 0.280 kg

If the circuit board holder is to be used with universal ball joint
base 9-251, we recommend that the combination is used with
angular adapter 9-255 or with rapid turning device 9-257 in order
to obtain a larger turning circle.

9-254 **Universal screw-on plate**
Slots made for commonly used standard bolts, for holding of e. g.
tuner, line output transformer, small loudspeaker etc. or prototypes
Weight: 0.120 kg

9-255 **Angular adapter**
to be used as an additional attachment with every work mount,
permits an even larger turning circle.
Weight: 0.095 kg

9-260 **BERNSTEIN SPANNFIX-VARIO** assembly vice

5-piece set
comparable with 9-250
only 9-251 Universal clamp ball joint base is changed into 9-261
Weight: 2.000 kg

9-261 **SPANNFIX bench mounted base with universal ball joint and
threaded stud M 12 x 1.5 for permanent mounting using bolts**
Size of base: 150 x 105 mm
Weight: 0.800 kg

All parts can also be obtained individually.

