


Part Number: 508

Type	Size	Rating	Description
Incandescent	T5	24V 1.2W	T-1½ Wedge Base lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
28	37	43	49	5.0	6.3	7.5	1,000@24V

Notes:

- 1 **Base Type** W2x4.6d
- 2 **Filament Shape** C-2F
- 3 **Lamp Marking** CML 24V 1.2W
- 4 **Bead Colour** White or Clear
- 5 **Environmental** RoHS & REACH SVHC compliant