

out notice and replaces all data sheets previously supplied. I he information supplied is believed to be accurate built the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from megligence or where the Group was aware of the possibility of sub loss or damage resulting list or any consulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. @ Premier Farnell pic 2008.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.


DRAWN BY:	DATE:	DRAW	ING TITLE:							
Jagan	11/02/08			Dual	In Line Switches	- En	d Stacka	able	Э	
CHECKED BY:	DATE:	SIZE	SIZE DWG NO. ELECTRONIC FILE							REV
Suresh	11/02/08	A		M10000815		EI-EIF	RDWG			Α
APPROVED BY:	DATE:	\vdash								
G.Cook	26/02/08	SCAL	LE: NTS		U.O.M.: mm (Inches)		SHEET:	1	OF	5

	PART NO.		REVISIONS										
🔊 multicomp	MCEI Series	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE			
		-	A	RELEASED	Jagan	11/2/08	Suresh	11/2/08	G. C	26/2/08			

Specifications: Mechanical:	
Mechanical life	: 2,000 operations.
Maximum operating force	: 1,000gf.
Stroke	: 1.0mm
Operating temperature range	: -20 to +85°C.
Storage temperature range Electrical:	: -40 to +85°C.
Electrical life	: 2,000 cycles.
Rating	: 25mA, 24V dc.
Minimum contact resistance	: 100mΩ at 500V dc.
Maximum insulation resistance	: 100MΩ at 500V dc.
Dielectric strength	: 500V ac/1 minute.
Contact arrangement Materials:	: 1 pole throw.
Base and cover	: UL 94V-0 Nylon high temperature thermoplastic. Colour : Black.
Actuator	: UL 94V-0 LCP high temperature thermoplastic. Colour : White.
Contact	: Alloy copper with gold plated.
Terminal	: Brass with gold plated.
Таре	: Kapton.

(the Group) or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE	Jagan	11/02/08		Dual In Line Switches	- End	Stackable	
believed to be accurate but the Group assumes no responsibility for its accuracy or	SPECIFIED,	CHECKED BY:	DATE:	SIZE DWG NO.		ELECT	RONIC FILE	REV
completeness, any error in or omission from it or for any use made of it. Users of this lata sheet should check for themselves the Information and the suitability of the proc tcst for their purpose and not make any assumptions based on information included	DIMENSIONS ARE FOR REFERENCE	Suresh	11/02/08	Δ	M10000815	EI-EIR DWG		A
omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit	PURPOSES ONLY.	APPROVED BY:	DATE:				_	
or restrict the Group's liability or death or personal injury resulting from this medigence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.		G.Cook	26/02/08	SCALE: NTS	U.O.M.: mm (Inches)		SHEET: 2	OF 5

	PART NO.		REVISIONS									
🐼 multicomp		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
	MCEI Series	-	А	RELEASED	Jagan	11/2/08	Suresh	11/2/08	G. C	26/2/08		



Soldering Process:

Wave soldering: Recommended solder temperature at 500°F (260°C) maximum of 5 seconds for through hole type. **Hand soldering:** Use a soldering iron of 30 watts, controlled at 350°C approximately maximum 5 seconds while applying. **Reflow soldering:** When applying reflow soldering, the peak temperature or the reflow Oven should be set at 260°C maximum. Do not wash the switch except top tape sealed type, which suitable for spray cleaning method from top of the s/w.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with-	UNLESS OTHERWISE	Jagan	11/02/08		Dual In Line Switches	- End Stackable	
out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this	SPECIFIED,	CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV
data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or	DIMENSIONS ARE	Suresh	11/02/08	Δ	M10000815	EI-EIR DWG	A
 omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit 	PURPOSES ONLY.	APPROVED BY:	DATE:				
or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.		G.Cook	26/02/08	SCALE: NTS	U.O.M.: mm (Inches)	SHEET: 3 O	0F 5

	PART NO.		REVISIONS										
🐼 multicomp			REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE			
	MCEI Series	-	А	RELEASED	Jagan	11/2/08	Suresh	11/2/08	G. C	26/2/08			

Specification Table


Number of Positions	Dimensions (A)	Dimensions (B)	Part Number
2	4.98 (0.196)	2.54 (0.100)	MCEI-02
3	7.52 (0.296)	5.08 (0.100)	MCEI-03
4	10.06 (0.396)	7.62 (0.300)	MCEI-04
5	12.60 (0.496)	10.16 (0.400)	MCEI-05
6	15.14 (0.596)	12.70 (0.500)	MCEI-06
7	17.68 (0.696)	15.24 (0.600)	MCEI-07
8	20.22 (0.796)	17.78 (0.700)	MCEI-08
9	22.76 (0.896)	20.32 (0.800)	MCEI-09
10	25.3 (0.996)	22.86 (0.900)	MCEI-10
12	3.0.38 (1.196)	27.94 (1.190)	MCEI-12
2	4.98 (0.196)	2.54 (0.100)	MCEIR-02
3	7.52 (0.296)	5.08 (0.100)	MCEIR-03
4	10.06 (0.396)	7.62 (0.300)	MCEIR-04
5	12.60 (0.496)	10.16 (0.400)	MCEIR-05
6	15.14 (0.596)	12.70 (0.500)	MCEIR-06
7	17.68 (0.696)	15.24 (0.600)	MCEIR-07
8	20.22 (0.796)	17.78 (0.700)	MCEIR-08
9	22.76 (0.896)	20.32 (0.800)	MCEIR-09
10	25.3 (0.996)	22.86 (0.900)	MCEIR-10
12	3.0.38 (1.196)	27.94 (1.190)	MCEIR-12

Dimensions : Millimetres (Inches)

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with	UNLESS OTHERWISE	Jagan	11/02/08] Dua	al In Line Switches	- End Stackable	
out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this	SPECIFIED,	CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV
data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or	DIMENSIONS ARE	Suresh	11/02/08	Δ	M10000815	EI-EIR DWG	Α
omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit	PURPOSES ONLY.	APPROVED BY:	DATE:				
Possibility of social roles of carrage ansing) is excluded. This will not operate to infinit restrict the Group's liability for death or personal injury resulting from its negligence. PC MULTICOMP is the registered trademark of the Group. © Premier Famell plc 2008.		G.Cook	26/02/08	SCALE: NTS	U.O.M.: mm (Inches)	SHEET: 4 C	DF 5

	PART NO.		REVISIONS									
🐢 multicomp		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
	MCEI Series	-	А	RELEASED	Jagan	11/2/08	Suresh	11/2/08	G. C	26/2/08		

Part Number Explanation:



Terminal Type	: I = Through Hole Type.
Actuator Type	: R = Recessed Actuator.
	= Raised Actuator.
Number of Positions	: 02, 03, 04, 05, 06, 07, 08, 09, 10, 12 Positions.

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
nformation purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with- jut notice and replaces all data sheets previously supplied. The Information supplied is	UNLESS OTHERWISE	Jagan	11/02/08] C	Dual In Line Switches	- End Stackable	
	SPECIFIED,	CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV
data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or	DIMENSIONS ARE	Suresh	11/02/08	Δ	M10000815	EI-EIR DWG	A
childed. Elability for loco of damage recalling north any forable of the internation of	eliance on the Information or here the Group was aware of d. This will not operate to limit vesulting from its negligence.		DATE:				<u> </u>
or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2008.			26/02/08	SCALE: NTS	U.O.M.: mm (Inches)	SHEET: 5 O	DF 5