


PRODUCT DATA SHEET

Part Number: 382

Type	Size	Rating	Description
Incandescent	T6	14V 80mA	T-1¾ Midget Flange Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
14	72	80	88	2.8	3.8	4.8	15,000

Notes:

- 1

Base Type

Nickel plated SX6s base to BS EN 60061-1
- 2

Filament Shape

C-2F
- 3

Lamp Marking

CML382 14V 80mA engraved or durable ink stamped on base shell
- 4

Environmental

RoHS & REACH SVHC compliant