


Part Number:

912-002LF

Type	Size	Rating	Description
Incandescent	T15	12.8V 1A	T-5 Wedge Base Lamp



Dimensions in millimetres ( ) reference value only

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12.8	900	1000	1100	-	150	-	1,000

Notes:

- Base Type** W2.1x9.5d special
- Filament Shape** C-2R
- Bead colour** White or clear
- Lamp Marking** 912 with a manufacturing date code
- Environmental** RoHS & REACH SVHC compliant