


Part Number : **1860225W3D**

Type	Size	Rating	Description
LED	T10	12V AC/DC	10mm Bayonet Starled

Dimensions(mm):



Part #	Colour	Voltage(V)	Current(mA)	Intensity(mcd)
1860225W3D	White diffuse	12	7	800

**Notes:**

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Lamp base in accordance with BS EN 60061-1:BA9s
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Voltage tolerance ±10%
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 The plastic(polycarbonate) has limited chemical resistance
- 8 RoHS & REACH SVHC compliant

Issue # 1 : 13Apr12