Dual Operational Amplifier, 7 MHz Bandwidth with Shutdown

NCS20282

The NCS20282 high precision op amp features a wide bandwidth along with shutdown. These amplifiers provide low bias current useful for transimpedance applications. The wide bandwidth eases the design of active filters. The NCS20282 is specified for operation from -40° C to $+125^{\circ}$ C.

Features


High Bandwidth: 7 MHz typicalLow Bias Current: 50 pA typical

Rail-to-Rail Input/Output
Shutdown Current: 1 μA max
Offset Voltage: 1.5 mV max
Offset Drift: 10 μV/°C max
Supply Voltage: 2.5 V to 5.5 V

 These Devices are Pb-free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Transducer Applications
- Sensor Conditioning
- Medical Instrumentation
- Impedance Sensing





ON Semiconductor®

www.onsemi.com





MARKING DIAGRAM




AAA = Specific Device Code
A = Assembly Location

Y = Year W = Work Week

(Note: Microdot may be in either location)

PIN CONNECTIONS



Package Bottom View (Bump Up)

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 9 of this data sheet.

This document contains information on some products that are still under development. ON Semiconductor reserves the right to change or discontinue these products without notice.

 Table 1. ABSOLUTE MAXIMUM RATINGS Over operating free-air temperature, unless otherwise stated.

| Parameter | Rating | Unit V | |
|---------------------------------------|------------------------------|-----------|--|
| Supply Voltage (VDD- VSS) | 7 | | |
| INPUT AND OUTPUT PINS | • | | |
| Input Voltage (Note 1) | (V _{SS} – 0.5) to 7 | V | |
| Input Current (Note 1) | ±5 | mA | |
| Output Pin Voltage, Disabled | 7 | V | |
| Output Short Circuit Current (Note 2) | Continuous | | |
| TEMPERATURE | | | |
| Operating Temperature | -40 to +125 | °C | |
| Storage Temperature | −65 to +150 | °C | |
| Junction Temperature | +150 | °C | |
| ESD RATINGS (Note 3) | | | |
| Human Body Model (HBM) | 2000 | V | |
| Charged Device Model (CDM) | 1000 | V | |
| OTHER RATINGS | | | |
| Latch-up Current (Note 4) | 100 | mA | |
| MSL | Level 1 | | |
| | • | | |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. The input voltage at any pin may exceed the voltage shown if the current at that pin is limited to 5 mA.
- Short-circuit to ground.
- This device series incorporates ESD protection and is tested by the following methods: ESD Human Body Model tested per JEDEC standard JS-001-2017 ESD Charged Device Model tested per JEDEC standard JS-002-2014
- 4. Latch-up Current tested per JEDEC standard: JESD78

Table 2. THERMAL INFORMATION

| Parameter | Symbol | Cu Area mm ² | 1.0 oz | 2.0 oz | Unit |
|---------------------|---------------|-------------------------|--------|--------|------|
| Thermal Resistance | Θ_{JA} | 10 | 301 | 263 | °C/W |
| Junction to Ambient | | 25 | 263 | 230 | |
| | | 40 | 246 | 215 | |
| | | 80 | 229 | 204 | |
| | | 140 | 220 | 196 | |
| | | 250 | 211 | 188 | |
| | | 350 | 206 | 183 | |
| | | 500 | 200 | 179 | |
| | | 650 | 197 | 175 | |
| | | 800 | 194 | 173 | |

NOTE: Four layer JSEC JESD51-7

Table 3. OPERATING CONDITIONS

| Parameter | Symbol | Range | Units |
|---|-----------------|----------------------|-------|
| Supply Voltage (V _{DD} – V _{SS}) | V _S | 2.5 to 5.5 | V |
| Specified Operating Temperature Range | T _A | -40 to +125 | °C |
| Input Common Mode Voltage Range | V _{CM} | V_{SS} to V_{DD} | V |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

Table 4. ELECTRICAL CHARACTERISTICS: $V_S = 2.5 \text{ V}$ to 5.5 V At $T_A = +25^{\circ}\text{C}$, $R_L = 10 \text{ k}\Omega$, $V_{CM} = V_{OUT} =$ midsupply, Enable input connected to V_{DD} , unless otherwise noted. **Boldface** limits apply over the specified temperature range, $T_A = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$, guaranteed by characterization and/or design.

| Parameter | | Symbol | Condit | ions | Min | Тур | Max | Units |
|-----------------------------------|-------------------------|--------------------------|---|-------------------------------|-----|----------------------|---------------------|--------------------|
| INPUT CHARACTERISTICS | 1 | • | - | | | - | | - |
| Offset Voltage | | Vos | | | | 300 | 1500 | μV |
| Offset Voltage Drift vs Temp | | $\Delta V_{OS}/\Delta T$ | | | | 2 | 10 | μV/°C |
| Input Bias Current (Note 5) | | I _{IB} | | | | 50 | 800 | pA |
| Input Offset Current | | I _{OS} | | | | 10 | | pА |
| Input Common-Mode Voltag | e Range | V _{CM} | | | | V_{SS} to V_{DD} | | V |
| Common Mode Rejection Ra | | CMRR | $V_{CM} = -0.1V \text{ to}$ | (V _{DD} +0.1V) | 66 | 86 | | dB |
| Input Resistance | | R _{IN} | Differe | | | 10 | | GΩ |
| | | | Common | Mode | | 10 | | 1 |
| Input Capacitance | | C _{IN} | Differe | ntial | | 2 | | pF |
| | | | Common | Mode | | 5 | | |
| OUTPUT CHARACTERISTIC | cs | | - | • | | • | | • |
| Open Loop Voltage Gain | | A _{VOL} | 0.4 V ≤ V _{OUT} ≤ | V _{DD} – 0.4 V | 96 | 116 | | dB |
| Closed Loop Output Impeda | nce | Z _{OUT_CL} | See Figu | | | See Figure 23 | | Ω |
| Output Voltage High, Refere | nced to V _{DD} | V _{OH} | | | | V _{DD} -3 | V _{DD} -10 | mV |
| Output Voltage Low, Referen | ced to V _{SS} | V _{OL} | | | | V _{SS} +6 | V _{SS} +10 | mV |
| Short Circuit Current (Note 5 |) | I _{SC} | Sinking C | Current | | 10 | 15 | mA |
| | | | Sourcing (| Current | | 10 | 15 | 1 |
| Capacitive Load Drive (Note | 5) | C _L | | | | 100 | 300 | pF |
| DYNAMIC PERFORMANCE | | | | | | | | |
| Gain Bandwidth Product (No | te 5) | GBW | $V_S = 3$ $R_L = 10 \text{ k}\Omega$, C | V; C _L = 100 pF | 5.4 | 7 | | MHz |
| Gain Margin | | A_{M} | C _L = 10 | 0 pF | | 50 | | dB |
| Phase Margin | | Ψ_{M} | C _L = 10 | 0 pF | | 55 | | 0 |
| Slew Rate | | SR | A _V = | +1 | | 5 | | V/μs |
| Overload Recovery Time | | t _{OR} | $V_{IN} X A_V > V_S$ | | | 1 | | μs |
| NOISE PERFORMANCE | | | | | | | | |
| Voltage Noise Density | | e _N | f _{IN} = 10 | kHz | | 20 | | nV/√ Hz |
| Current Noise Density | | i _N | f _{IN} = 1 Hz | | | 300 | | fA/√ Hz |
| POWER SUPPLY | | | | | | | | |
| Power Supply Rejection Rati | 0 | PSRR | | | 90 | 120 | | dB |
| Shutdown Enable Time (Notes 5, 6) | | t _{ON} | | | | 30 | 50 | μs |
| Shutdown Disable Time (Note 6) | | t _{OFF} | | | | 30 | | μs |
| Shutdown Leakage Input | | | V _{IN} = V _S + | 400 mV | | | 500 | nA |
| | Output | | V _{OUT} = V _S +1 V | | | | 500 |] |
| Enable Input Threshold Voltage | | V _{th(EN)} | Operating | | 1.3 | | | V |
| | | | Disabled | | | | 0.5 | |
| Enable Input Leakage Current | | I _{Enable} | Enable = + 5.0 V | | | 1.1 | | μΑ |
| | | | Enable = V _{SS} | | | 1.1 | | |
| Quiescent Current | | IQ | Per Channel | Quiescent | | 850 | 1300 | μΑ |
| | | <u> </u> | No load | Shutdown | | 0.3 | 1 | |

the point at which the output voltage reaches the 10% (disable) or 90% (enable) level.

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

^{5.} Guaranteed by design and/or characterization
6. Shutdown Disable Time (t_{OFF}) and Enable Time (t_{ON}) are defined as the time between the 50% point of the signal applied to the EN pin and




Figure 1. CMRR vs. Frequency

Figure 2. PSRR vs. Frequency




Figure 3. Input Bias Current vs. V_{CM} at $V_S = 2.5 \ V$

Figure 4. Input Bias Current vs. V_{CM} at $V_S = 3.3 \ V$




Figure 7. Input Offset Current vs. V_{CM} at $V_S = 3.3 \text{ V}$

Figure 8. Input Offset Current vs. V_{CM} at $V_S = 5.5 \text{ V}$





Figure 13. Non Inverting Small Signal Transient Response

Figure 14. Non Inverting Large Signal Transient Response



0.08 0.06 0.04 **VOLTAGE (V)** $A_V = -1 \text{ V/V}$ 0.02 C_L = 15 pF $V_S = 2.5 V$ $C_L = 100 \text{ pF}$ R_L = 10 $K\Omega$ -0.02 -0.04-0.06 -0.08-0.10 0 -2 2 4 6 8 10 12 TIME (µs)




Figure 17. Inverting Small Signal Transient Response




Figure 19. Inverting Large Signal Transient Response

Figure 18. Inverting Small Signal Transient Response




Figure 20. Inverting Large Signal Transient Response




Figure 21. Enable Turn-On Time

Figure 22. Disable Turn-Off Time




Figure 23. Closed Loop Output Impedance

Figure 24. Voltage Noise Density vs. Frequency




Figure 25. 0.1 Hz to 10 Hz Noise


DEVICE ORDERING INFORMATION


| Device | Marking | Bump Type | Case Outline | Package | Shipping [†] |
|-------------------------------------|---------|-----------|--------------|----------------------|-----------------------|
| NCS20282FCTTAG | AAA | Sn Plate | 567UW | WLCSP-9 (Pb-Free) | 5000 / Tape & Reel |
| NCS20282FCSTAG* (In Development) | AAA | SAC 405 | 567YD | WLCSP-9 (Pb-Free) | 5000 / Tape & Reel |


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

WLCSP9, 1.02x1.02x0.33 CASE 567UW **ISSUE A**








- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. COPLANARITY APPLIES TO THE SPHERICAL CROWNS OF THE SOLDER BALLS.

| | MILLIMETERS | | | | | | |
|-----|-------------------|-------------|------|--|--|--|--|
| DIM | MIN | MIN NOM MAX | | | | | |
| Α | | | 0.33 | | | | |
| A1 | 0.04 | 0.06 | 0.08 | | | | |
| A2 | 0.23 REF | | | | | | |
| b | 0.180 0.200 0.220 | | | | | | |
| D | 0.99 | 1.02 | 1.05 | | | | |
| E | 0.99 | 1.02 | 1.05 | | | | |
| е | 0.35 BSC | | | | | | |

RECOMMENDED SOLDERING FOOTPRINT*




DIMENSIONS: MILLIMETERS

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS


WLCSP9, 1.02x1.02x0.441 CASE 567YD



NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: MILLIMETERS 2.
- COPLANARITY APPLIES TO THE SPHERICAL CROWNS OF THE SOLDER BALLS.

| | MILLIMETERS | | | |
|-----|-------------------|-------|-------|--|
| DIM | MIN. NDM. MAX. | | | |
| Α | 0.441 | | | |
| A1 | 0.133 | 0.153 | 0.173 | |
| A2 | 0.255 REF | | | |
| b | 0.183 0.203 0.223 | | | |
| D | 0.99 | 1.02 | 1.05 | |
| E | 0.99 | 1.02 | 1.05 | |
| е | 0.35 BSC | | | |



RECOMMENDED MOUNTING FOOTPRINT

For additional information on our Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference Manual, SDLDERRM/D.

ON Semiconductor and 🕠 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative