


RoHS
Compliant



Scope

This specification is applied to thermoelectric modules
Revision of these specifications is carried out after consent

Specifications

Parameters		Remarks
Internal Resistance	5Ω ±10%	Note-1
I max.	2.8A	Note-2
V max.	15.7V	Note-3
-	Th = 27°C Th = 50°C	-
Q max.	8.7 W 9.6 W	Note-4
ΔT max.	95°C 105°C	Note-5
Solder melting point		Note-6
Maximum compress		Note-7

Note-1 : Measured by AC 4 - terminal method at 25°C

Note-2 : Maximum current at ΔT max.

Note-3 : Maximum voltage at ΔT max.

Note-4 : Maximum cooling capacity at I max. V max. and ΔT = 0°C

Note-5 : Maximum temperature difference at I max. V max. and Q = 0 W

(Maximum parameters are measured in a vacuum 1.3 P)

Note-6 : The solder melting point of thermoelectric module

Note-7 : Recommended maximum compression (not destruction limit)

Specification Table

Thot = 27°C

I max. (A)	U max. (V)	Qc max. W	dT max. °C	A	B	H	Part Number
2.8	-	8.7	95	30	30	3.98	MCPK2-15828NC-S


Dimensions : Millimetres

PK2 Modules are high performance double stage modules, silicone sealed for moisture protection, for applications where high cooling capacity is needed at high operation temperature

Recommended operation temperature up to 90°C for long life

Recommended operating current 0.7 I max. for long life

Diagram



Part Number Table

Description	Part Number
Thermoelectric Peltier Cooler Module, Double Stage, 8.7W, 2.8A	MCPK2-15828NC-S

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro