


Fuse plug - PV-PRO/M/F-200/F-1000/19 - 1220866

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Photovoltaic connector, Range of articles: SUNCLIX, Fuse plug, color: black, nom. voltage: 1000 V DC (bis 4000m ü. NN), rated current: 19 A, Connection method: SUNCLIX PV connector. SUNCLIX fuse element for protecting panels and devices in photovoltaic systems

Key Commercial Data

Packing unit	8 pc
Minimum order quantity	8 pc
GTIN	 4 063151 308148
GTIN	4063151308148
Weight per Piece (excluding packing)	22.220 g
Sales Key	ABLBEA

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 55 °C (Deviating ambient temperatures possible depending on the current carrying capacity/derating curve)
Ambient temperature (assembly)	-25 °C ... 50 °C

General

Standards/regulations	2PFG 2380-2014-02 in progress
Insertion force	45 N ±10 N
Disconnect force	250 N ±100 N
Rated surge voltage	12 kV
Degree of pollution	2
Degree of protection	IP66 / IP68 (2 m / 24 h)
Rated voltage	1000 V
Fuse-link nominal current	20 A DC (Nominal current of the fuse-link)
Fuse adapter nominal current	19 A DC (Nominal current of the item)
Protection class	II

Material

Color	black
-------	-------

Connection data

Fuse plug - PV-PRO/M/F-200/F-1000/19 - 1220866

Technical data

Connection data

Connection method	SUNCLIX PV connector
-------------------	----------------------

Standards and Regulations

Standards/specifications	2PFG 2380-2014-02 in progress
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 9.0	27440107
------------	----------