1W Isolated DC to DC Converters - Dual Output multicomp

1W isolated DC-DC converter Fixed input voltage, unregulated dual output

RoHS **Compliant**





Features

- · Continuous short-circuit protection
- No-load input current as low as 8mA
- Operating ambient temperature range: -40°C to +105°C
- High efficiency up to 85%
- I/O isolation test voltage: 1.5k VDC
- Industry standard pin-out

These series are specially designed for applications where two isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits.

Selection Guid	de					
	Input Voltage (VDC)	Output		Full Load Efficiency	Compositive Lond(v.E)*	
Part Number	Nominal (Range)	Voltage Current (mA) (VDC) Max./Min.		Full Load Efficiency (%) Min./Typ.	Capacitive Load(µF)* Max.	
MPA1205XT-1W		±5	±100/±10	78/82	1200	
MPA1212XT-1W	12 (10.8 to 13.2)	±12	±42/±5	79/83	220	
MPA1215XT-1W		±15	±34/±4	79/83	220	
MPA1224XT-1W		±24	±21/±3	81/85	100	
MPA1515XT-1W	15 (13.5 to 16.5)	±15	±34/±4	79/83	220	
MPA2405XT-1W		±5	±100/±10	76/82	1200	
MPA2412XT-1W	24 (24 6 to 26 4)	±12	±42/±5	77/83	220	
MPA2415XT-1W	24 (21.6 to 26.4)	±15	±34/±4	77/83	220	
MPA2424XT-1W		±24	±21/±3	79/85	100	

Item		Operating Conditions	Min.	Тур.	Max.	Unit
		±5VDC output	-	102/8	107/	
	12V input	±9VDC/±12VDC/±15VDC output	-	101/8	106/	1
Input Current		±24VDC output	-	99/8	103/	1
(full load / no-load)	15V input		-	81/8	85/] _{mA}
	24) / immt	±5VDC/±9VDC/±12VDC/±15VDC output	-	51/8	55/	
	24V input	±24VDC output	-	50/8	53/	
Reflected Ripple Current*			-	30	-	
_		12VDC input			18	
Surge Voltage(1sec. max.)	15VDC input		-0.7	-	21	V DC
voltage(13cc. Illax.)	24VDC input				30	
Input Filter		Capacitance filter				
Hot Plug				Unavailal	ble	



1W Isolated DC to DC Converters - Dual Output



Output Specifications

Item	Operating Conditions		Min.	Тур.	Max.	Unit
Voltage Accuracy			See output	regulation	n curves (l	Fig. 1)
Linear Regulation	Input voltage change:	±1%		-	1.2	-
		±5VDC output		10	15	
	10% -100% load	±9VDC output		8	10	%
Load Regulation		±12VDC output		7	10	
		±15VDC output	-	6	10	
		±24VDC output		5	10	
Ripple & Noise*	20MHz bandwidth	±5VDC/±9VDC/±12VDC/± 15VDC output		30	75	mVp-p
		±24VDC output		50	100	
Temperature Coefficient	100% load			±0.02	-	%/°C
Short-Circuit Protection			Contir	nuous, se	f-recovery	/

Note: * The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.

General Specifications								
Item	Operating Conditions	Min.	Тур.	Max.	Unit			
Isolation	Input-output electric strength test for 1 minute with a leakage current of 1mA max.	1500	-	-	VDC			
Insulation Resistance	Input-output resistance at 500VDC	1000	-	-	ΜΩ			
Isolation Capacitance	Input-output capacitance at 100kHz/0.1V	-	20	-	pF			
Operating Temperature	Derating when operating temperature≥100°C, (see Fig. 2)	-40	-	105				
Storage Temperature		-55	-	125	°c			
Case Temperature Rise	Ta=25°C	-	30	-]			
Storage Humidity	Non-condensing	5	-	300]			
Reflow Soldering Temperature*		Peak temp.≤245°C, maximum duration time≤60s over 217°C						
Switching Frequency	vitching Frequency Full load, nominal input voltage		260	-	kHz			
MTBF	MIL-HDBK-217F@25°C	3500	-	_	k hours			
Moisture Sensitivity Level (MSL)	IPC/JEDEC J-STD-020D.1		l	_evel 1				

Mechanical Specifications						
Case Material	Black plastic; flame-retardant and heat-resistant (UL94 V-0)					
Dimensions	15.24 x 11.40 x 7.25 mm					
Weight	1.4g(Typ.)					
Cooling Method	Free air convection					




1W Isolated DC to DC Converters - Dual Output multicomp

Electromagnetic Compatibility (EMC)


Emissions	CE	CISPR32/EN55032 CLASS B(see Fig. 4 for recommended circuit)
EIIIISSIOIIS	RE	CISPR32/EN55032 CLASS B(see Fig. 4 for recommended circuit)
Immunity ESD IEC/EN61000-4-2 Contact ±6kV		IEC/EN61000-4-2 Contact ±6kV perf. Criteria B

Typical Performance Curves



Temperature Derating Curve 120 100 Output PowerPercentage(%) 80 60 Safe Operating Area 20 0 -40 40 100105 120 Operating Temperature (°C)

Fig. 1









Fig. 2









1W Isolated DC to DC Converters - Dual Output multicomp PRO



Design Reference

Typical application

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig.3.

Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1.




Table 1: Recommended input and output capacitor values

	Vin	Cin Vo		Cout
	12VDC	2.2µF/25V	±5VDC	4.7µF/16V
	15VDC	2.2µF/25V	±9VDC	1µF/16V
	24VDC	1μF/50V	±12VDC	1µF/25V
	-	-	±15VDC	0.47µF/25V
ſ	-	-	±24VDC	0.47µF/50V

2. EMC (CLASS B) compliance circuit





Table 2: EMC recommended circuit value table

	C1	4.7μF /50V
	C2	4.7μF /50V
Emissions	CY	270pF/2kV
	C3	Refer to the Cout in table 1
	C4	Refer to the Cout in table 1
	LDM	6.8µH

Dimensions and Recommended Layout



2.10 [0.083] op View 1.00 [0.039] -2.54 [0.100]

Note: Grid 2.54*2.54mm


Pin-Out						
Pin	Function					
1	GND					
2	Vin					
4	0V					
5	-Vo					
7	+Vo					
10	NC					

NC: Pin to be isolated from circuitry



1W Isolated DC to DC Converters - Dual Output multicomp PRO

Tape and Reel Info



Package Type	Pin	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SMD	6	500	330.0	24.5	15.64	12.4	7.45	16.0	24.0	Q1

Notes:

- 1. If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- 2. The maximum capacitive load offered were tested at input voltage range and full load;
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 4. All index testing methods in this datasheet are based on our company corporate standards;
- 5. We can provide product customization service, please contact our technicians directly for specific information;
- 6. Products are related to laws and regulations: see "Features" and "EMC";
- 7. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

