
D-Sub H/D Plug to Free End VGA, 15 Way


pro-signal



RoHS Compliant

Diagram





Note:

Material:

Cable: {[7/0.12TC×1C+S(30/0.1TC)+PVC]×3PCS+7/0.12TC×9C+AM+7/0.12BC+128/0.12ALM+Black PVC Jacket

OD: 8.2±0.2mm

Cable Marking: Low Voltage Computer Cable 80°C 30V

P1: HDB 15Pin Male: Solder Type, Blue PBT Insulation, Gold Flash Contacts, Nickel Plated

HDB15 Open: Tin Plate. Hood Molded Black PVC.

Thumb Screw to be Molded Black PVC.

Part Number Table

Description	Length (L)	Part Number
D-Sub H/D Plug to Free End, VGA, 15 Way	15m ±0.2m	PSG91368
	20m ±0.3m	PSG91369

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

