



TE Internal #: BKA199N00550200000

Standard Circular Connectors, Cable-to-Cable, Power & Signal,
Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy,
PBT GF, 23 Shell Size

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Sealable: **No**

Circuit Application: **Power & Signal**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Shell Plating Material: **Electrodeposited Nickel**

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Shell Type	Metal

Electrical Characteristics

Operating Voltage	630 VAC
-------------------	---------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

Dimensions

Cable Diameter Range	7.5 – 12 mm[.29 – .47 in]
----------------------	---------------------------

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power & Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Approved Standards	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # BSA078N00550235000 923 PLUG	 TE Part # C0-0236-000-000 DIGITAL CRIMPING TOOL, MID SIZE	 TE Part # C0-0201-000-000 CRIMPING TOOL MID-SIZE	 TE Part # C0-0009-000-000 POSITIONING INSERT FOR 2 MM CONTACTS
 TE Part # C0-0004-000-000 POSITIONING INSERT FOR 2 MM CONTACTS	 TE Part # C0-0252-000-000 POSITIONING INSERT FOR 1 MM CONTACTS		

Customers Also Bought

 TE Part #E75778-000 342A012-100-G05/86-0	 TE Part #1-1376009-1 H-HDR ASSY 8P FOR SEQUENTIAL T	 TE Part #8364194001 Single Wall CGPT Spool Heat Shrink Tubin	 TE Part #2255144-1 MINI SAHT D2000-M
 TE Part #BSA200N00420235000 923 PLUG	 TE Part #AKA874M1085151A000 617 EXTENSION, SPEEDTEC-READY	 TE Part #CUA480N00440050000 940 PLUG, ANGLED	 TE Part #2-178127-6 DYNAMIC 3100 REC HSG 6P K-YY

Documents

Product Drawings



923 EXTENSION, SPEEDTEC-READY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_BKA199N00550200000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_BKA199N00550200000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_BKA199N00550200000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BKA199N00550200000

English

Instruction Sheets

Instruction Sheet (non U.S.)

English