

61.039.11 ✓ ACTIVE


TE Internal #: 61-0039-011-000

Standard Circular Connectors, 58A Contact Current Rating (Max),
Power, Brass, 40 Shell Size, 0° Alignment Keyed, Metal, Pin

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **58 A**

Circuit Application: **Power**

Shell Base Material: **Brass**

Circular Connector Shell Size: **40**

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	58 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	40
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Circuit Application

Power

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

<p>TE Part # C0-0008-000-000 CRIMPING TOOL LARGE</p>	<p>TE Part # C0-0010-000-000 POSITIONING INSERT FOR 3.6 MM CONTACTS</p>	<p>TE Part # C0-0313-000-000 CRIMPING DEVICE HC20 IN CASE</p>
--	---	---


Customers Also Bought



TE Part #CZ3662-000
SETR14AI-SIDE-ENTRY-TINEL-LOCK-RING



TE Part #183253-000
TXR18AB00-2214AI



TE Part #041997-000
TXR18AB90-2214AI



TE Part #2358691-1
RESOLVER V23401-T1071-B101



TE Part #CSA263N00250001000
940 PLUG



TE Part #61-0107-011-000
CONTACT PIN 2 MM



TE Part #ASA046F0185050A000
617 PLUG, SPEEDTEC



TE Part #2280413-1
CERTI-CRIMP II SAHT

Documents

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_61-0039-011-000_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_61-0039-011-000_A.3d_igs.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_61-0039-011-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[61-0039-011-000](#)

English