



Application Tooling > Portable Crimp Tools

Tool Grade: **Commercial Crimp Tooling**Ratchet Configuration: **Operator Releasable & Adjustable**Die Sets Type: **Removable/Interchangeable**Specification Type: **TE Product Specification (114-)**TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET


TE Part # 962999-1
1,5MMD SOCKET CONTACT



TE Part # 962981-1
2,5MMD SOCKET CONTACT



TE Part # 962998-1
1,5MMD SOCKET CONTACT



TE Part # 962971-1
2,5MMD PIN CONTACT

TE Part # 1-1719188-0
DIA 1.5 SOCK CON,TERMINAL

TE Part # 1-1418497-0
DIA 1.5 SOCK CON TERMINAL

TE Part # 1-929967-3
STIFTKONT.2,5 M EDS

TE Part # 1-929968-3
STIFTKONT.2,5 M EDS

TE Part # 1-929974-3
BU-KONTAKT2,5 M EDS

TE Part # 1-929975-3
BU-KONTAKT2,5 M EDS

TE Part # 1-929983-1
STIFTKONTAKT 1,5MMD

<p>TE Part # 1-929983-2 STIFTKONTAKT 1,5MMD</p>	<p>TE Part # 1-929983-3 STIFTKONTAKT 1,5MMD</p>	<p>TE Part # 1-929984-1 STIFTKONTAKT 1,5MMD</p>	<p>TE Part # 1-929984-2 STIFTKONTAKT 1,5MMD</p>
<p>TE Part # 1-929984-3 STIFTKONTAKT 1,5MMD</p>	<p>TE Part # 1-962971-4 2,5MM SWS PIN CONTACT LOOSE PIECE</p>	<p>TE Part # 1-962972-0 2,5MM STIFTKONT EDS</p>	<p>TE Part # 1-962981-0 2,5MM PIN CONTACT SWS LOOSE PIECE</p>

Customers Also Bought

<p>TE Part #1-643075-5 Nylon PCB Connector Covers: 2.54 mm, MTA 100</p>	<p>TE Part #1734366-4 Std USB Type A, VT, T/H</p>	<p>TE Part #1-480350-0 01P CMNL CAP HSG F/H NATL</p>	<p>TE Part #1879623-9 H4 330R 0.1% 5PPM</p>
<p>TE Part #1-776262-2 AMPSEAL HEADERS</p>	<p>TE Part #1438618-1 GET .64 CONNECTOR SYSTEM, CONNECTOR HSG</p>	<p>TE Part #HDP24-24-35PN-L017 DEUTSCH HDP20 HOUSINGS</p>	<p>TE Part #1393304-5 V23134J0056X408-EV-CBOX</p>
<p>TE Part #1452410-1 COVER ASSY F.58 POS</p>	<p>TE Part #1-968408-2 FLA-ST-GH2,8X0,8 3P</p>		

Documents



Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[Bottoming Dies](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English