



Application Tooling > Spare & Wear Tooling



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 466900-1
[APPL,SCA 9SMPR055F062O S](#)

Customers Also Bought

TE Part #1658641-3
D-Sub Crimp: Plug, Signal, 50 Posn,
Pin Size 20, Shell Size 5

TE Part #1658608-4
IDC D-Sub: Plug Assembly, Low
Profile, Signal, 2.77 mm

TE Part #1490414-2
HYP10 SOLIS HD 6-4AWG INDENTER

TE Part #1-480705-2
06P UNML CAP HSG RED

TE Part #1-350767-9
03P UMNL V0 CAP HSG BLACK

TE Part #1-87456-3
18 MODIV HSG COMP DR .100CL

TE Part #YDTS26F17-08SNV001
Straight Plug: D38999, 17-08 Insert,
Electroless Nickel Plating

TE Part #102321-6
AMP-LATCH UNIVERSAL HEADERS

TE Part #1490413-2
HYP10 SOLIS HD 8AWG NEST

TE Part #1-456402-5
CRIMPER WIRE .055 F

Documents

Datasheets & Catalog Pages
[CRIMPING WHERE FORM MEETS FUNCTION](#)
English

Instruction Sheets
[Instruction Sheet \(U.S.\)](#)
English