Note: This datasheet may be out of date.

Please download the latest datasheet of BLF02RD331GNE# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLF02RD331GNE%23

"#" indicates a package specification code.

BLF02RD331GNED








< List of part numbers with package codes > BLF02RD331GNED BLF02RD331GNEB



Appearance & Shape









Features

- 1.Frequency specified filters are designed to reduce noise greatly at specified frequency. which greatly reduces the possibility of resonance and leaves signal wave forms undistorted. BLF series is effective in circuits without stable ground lines because BLF series does not need a connection to ground.
- 2.The nickel barrier structure of the external electrodes provides excellent solder heat resistance.
- 3.BLF02RD series is designed to have high impedance at 2.4GHz. Suitable for immunity noise suppression for LTE band, WiFi band.



Applications

Other Usage For general



Packaging Information

Packaging	Specifications	Standard Packing
		Quantity
D	180mm Paper Tape	15000
В	Bulk(Bag)	1000

1 of 3

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



BLF02RD331GNED

Note: This datasheet may be out of date.

Please download the latest datasheet of BLF02RD331GNE# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLF02RD331GNE%23

"#" indicates a package specification code.



Specifications

Shape	SMD	
Size Code (in inch)	01005	
Length	0.4mm	
Length Tolerance	±0.02mm	
Width	0.2mm	
Width Tolerance	±0.02mm	
Thickness	0.3mm	
Thickness Tolerance	±0.02mm	
Operating Temperature Range	-55°C to 125°C	
Mass(typ.)	0.125mg	
Number of Circuit	1	
Rated Current (at 85°C)	330mA	
Rated Current (at 125°C)	220mA	
DC Resistance(max.)	0.6Ω	
Impedance (at Target Frequency)	330Ω±40% (at 2.4GHz)	
Size Code (in mm)	0402	

2 of 3

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



BLF02RD331GNED


Note: This datasheet may be out of date.

Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=BLF02RD331GNE%23

"#" indicates a package specification code.







In operating temperature exceeding +85°C, derating of current is necessary for this series. Please apply the derating curve shown in chart according to the operating temperature.

Please download the latest datasheet of BLF02RD331GNE# from the official website of Murata

Derating of Rated Current



Impedance-Frequency Characteristics



Derating of Rated Current

Equivalent Circuit

3 of 3

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

