

Type 360410

Single terminal block, solderable, horizontal wire entry, open construction, double solder pins, screw brought down by hand

Technical Data

| | |
|---|----------------|
| A / AWG | 15 / 30 - 18 |
| Insulation co-ordination according to IEC 664-1 | |
| Protection category according to IEC 529 | |
| | IP00 |
| Tightening torque UL | 4.4 lb-in max. |
| Solder pin dimension | 2 x 1.0 mm |
| Recommended pc board hole dia. | Ø 1.5 mm |
| Solder pin length | 3.5 mm |

Type 360322

Single terminal block, solderable, horizontal wire entry, wire protector, open construction, double solder pins, screw brought down by hand

Technical Data



| | |
|---|--------------|
| A / AWG | 15 / 30 - 16 |
| A / AWG | 15 / 30 - 16 |
| Insulation co-ordination according to IEC 664-1 | |
| Protection category according to IEC 529 | |
| | IP00 |
| Tightening torque UL | 6 lb-in max. |
| Solder pin dimension | 2 x 1.0 mm |
| Recommended pc board hole dia. | Ø 1.5 mm |
| Solder pin length | 3.5 mm |

Dimensions in mm

1 mm = 0.0394 in.

Dimensions in mm

1 mm = 0.0394 in.



Part numbers (P/N)

Type 360410
P/N 360410

Part numbers (P/N)

Type 360322
P/N 360322