

Product Search Data Sheet



Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH501MQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH501MQ2%23

## "#" indicates a package specification code.

In Production AEC-Q200 RoHS REACH


< List of part numbers with package codes > DLW5ATH501MQ2K DLW5ATH501MQ2L

DLW5ATH501MQ2B



## Appearance & Shape





Packaging Information

Packaging	Specifications	Standard Packing Quantity
К	330mm Embossed Tape	2500
L	180mm Embossed Tape	700
В	Bulk(Bag)	100



## Features

1. Low profile(h=2.35mm max.)

2. Small size(5.0x3.6mm)

- 3 .Large Current Available (1.5Ato 4A)
- 4 .Operating Temperature Range -40°C to +125°C
- 5 .Reflow and Flow soldering Available

# Applications

Automotive Usage

Powertrain/Safety

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





# DLW5ATH501MQ2L

Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH501MQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH501MQ2%23

### "#" indicates a package specification code.



# Specifications

Shape	SMD
Size Code (in mm)	5036
Size Code (in inch)	2014
Length	5.0mm
Length Tolerance	±0.3mm
Width	3.6mm
Width Tolerance	±0.3mm
Thickness	2.2mm
Thickness Tolerance	±0.15mm
Common Mode Impedance (at 100MHz)	500Ω
Common Mode Impedance (at 100MHz) Tolerance	(Тур.)
Common Mode Impedance (at 10MHz)	35Ω
Common Mode Impedance (at 10MHz) Tolerance	min.
Rated Current	2A
Derating of Rated Current	Yes (Over 105°C) *For details, please check the derating diagram.
Rated Voltage	50Vdc
Withstanding Voltage	125Vdc
DC Resistance(max.)	0.034Ω
DC Resistance	0.034Ω max.
Insulation Resistance(min.)	10ΜΩ
Operating Temperature Range	-40°C to 125°C
Mass(typ.)	0.14g

Number of Circuit	1
Operating Temperature	
Range(Self-temperature rise	No
is included)	

2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.








Note: This datasheet may be out of date. Please download the latest datasheet of DLW5ATH501MQ2# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DLW5ATH501MQ2%23

#### "#" indicates a package specification code.







Impedance-Frequency Characteristics

In operating temperature exceeding +105°C, derating of current is necessary for DLW5ATH\_MQ2 series. Please apply the derating curve shown in chart according to the operating temperature.






Derating of Rated Current



Impedance-Frequency Characteristics (Main Items)



### Equivalent Circuit

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



without advance notice. Please check with our sales representatives or product engineers before ordering.