



P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BVDSS	RDS(ON) max	Package	I _D T _A = +25°C
-25V	27mΩ @ V _{GS} = -4.5V	U-DFN2020-6	-6.7A
-25V	40mΩ @ V _{GS} = -1.8V	(Type E)	-5.4A

Description

This new generation MOSFET has been designed to minimize the onstate resistance (RDS(ON)) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

Applications

- Load Switching
- Battery Management Application
- Power Management Functions

Features

- Low R_{DS(ON)} Ensures on State Losses are Minimized
- 0.6mm Profile Ideal for Low Profile Applications
- PCB Footprint of 4mm²
- ESD Protected Gate
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at


https://www.diodes.com/products/automotive/automotive-products/.

 This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.


https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Case: U-DFN2020-6
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208@3
- Weight: 0.001 grams (Approximate)









Ordering Information (Note 4)

Part Number	Case	Packaging
DMP2039UFDE-7	U-DFN2020-6 (Type E)	3,000/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information

Site 1



P9 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Key

zaio codo itoj												
Year	2011		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	Υ		Н		J	K	L	М	N	0	Р	R
)		
								I _				
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

Site 2



P9 = Product Type Marking Code YWX = Date Code Marking Y = Year (ex: 0 = 2020) W = Week (ex: a = Week 27; z Represents Week 52 and 53) X = Internal Code (ex: U = Monday)

Date Code Key

Year	2011		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	1		0	1	2	3	4	5	6	7	8	9
Week		1-	26			27-	-52			5	3	
Code		Α	-Z			a-z					Z	
Internal Code	Sur	1	Mon		Tue	W	ed	Thu		Fri		Sat
Code	Т		U		V	V	٧	Х		Υ		Z



Maximum Ratings (@ $T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	VDSS	-25	V		
Gate-Source Voltage	V _{GSS}	±8	V		
Continuous Drain Current (Note EVV 4 EV	lo	-6.7 -5.3	Α		
Continuous Drain Current (Note 5) V _{GS} = -4.5V	T _A = +25°C T _A = +70°C	lo	-8.3 -6.6	А	
Continuous Desis Correct (Note 5) V 4 0)	$T_A = +25$ °C $T_A = +70$ °C	lo	-5.4 -4.3	Α	
Continuous Drain Current (Note 5) V _{GS} = -1.8V	ID	-6.6 -5.2	А		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%	I _{DM}	-60	Α		
Continuous Source-Drain Diode Current			Is	-2.0	Α

Thermal Characteristics

Characteristic	Symbol	Value	Unit		
Total Power Dissipation (Note 5)	T _A = +25°C	D-	0.8	W	
Total Power Dissipation (Note 5)	$T_A = +70^{\circ}C$	PD	1.2	VV	
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	D	160	°C/W	
Thermal Resistance, Junction to Ambient (Note 3)	t<5s	RθJA	104	C/VV	
Total Bower Dissination (Note 6)	$T_A = +25$ °C	D-	2.0	W	
Total Power Dissipation (Note 6)	$T_A = +70$ °C	PD	2.9	VV	
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	RеJA	63	°C/W	
Thermal Resistance, Junction to Ambient (Note 6)	t<5s	КөЈА	42	C/VV	
Thermal Resistance, Junction to Case (Note 6)	Steady State	$R_{\theta JC}$	10.8	°C/W	
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C	

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)			•		•	
Drain-Source Breakdown Voltage	BV _{DSS}	-25	_	_	V	$V_{GS} = 0V, I_{D} = -250\mu A$
Zero Gate Voltage Drain Current	I _{DSS}	_	_	-1	μΑ	$V_{DS} = -25V, V_{GS} = 0V$
Gate-Source Leakage	Igss	_	_	±10	μΑ	$V_{GS} = \pm 8.0V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	V _{GS(TH)}	-0.4	_	-1.0	V	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$
			20	27		$V_{GS} = -4.5V$, $I_{D} = -6.4A$
Static Drain-Source On-Resistance	Pro/out		24	34	mΩ	$V_{GS} = -2.5V$, $I_D = -4.8A$
Static Diam-Source Off-Resistance	RDS(ON)		28	40	11152	$V_{GS} = -1.8V, I_{D} = -2.5A$
			33	70		$V_{GS} = -1.5V, I_{D} = -1.5A$
Forward Transfer Admittance	Y _{fs}		16	_	S	$V_{DS} = -5V$, $I_{D} = -4A$
Diode Forward Voltage	VsD		-0.7	-1.0	V	VGS = 0V, IS = -1A
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	Ciss	_	2530	_	pF	\/ 45\/ \/ 0\/
Output Capacitance	Coss		203	_	pF	V _{DS} = -15V, V _{GS} = 0V f = 1.0MHz
Reverse Transfer Capacitance	Crss		177	_	pF	1 = 1.0101112
Gate Resistance	Rg		9.1	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1.0MHz$
Total Gate Charge (V _{GS} = -4.5V)	Qg		28.2	_	nC	
Total Gate Charge (V _{GS} = -8V	Qg		48.7	_	nC	\/ 45\/ I- 40A
Gate-Source Charge	Qgs	_	3.2	_	nC	$V_{DS} = -15V, I_{D} = -4.0A$
Gate-Drain Charge	Q_{gd}	_	5.0	_	nC	
Turn-On Delay Time	td(ON)	_	15.1	_	ns	
Turn-On Rise Time	t _R	_	23.5	_	ns	$V_{DD} = -15V$, $V_{GS} = -4.5V$, $R_G = 1\Omega$,
Turn-Off Delay Time	tD(OFF)	_	137.6	_	ns	I _D = -4.0A
Turn-Off Fall Time	t _F	_	80.5		ns	


Notes:

^{5.} Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.

^{7.} Short duration pulse test used to minimize self-heating effect.

^{8.} Guaranteed by design. Not subject to production testing.












Fig. 7 Gate Threshold Variation vs. Ambient Temperature









Fig. 10 Typical Drain-Source Leakage Current vs. Voltage









Fig. 13 Transient Thermal Resistance



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN2020-6 (Type E)




	U-DFN2020-6 Type E							
Dim	Min Max Typ							
Α	0.57	0.63	0.60					
A1	0	0.05	0.03					
A3	_	1	0.15					
b	0.25	0.35	0.30					
b1	0.185	0.285	0.235					
D	1.95	2.05	2.00					
D2	0.85	1.05	0.95					
E	1.95	2.05	2.00					
E2	1.40	1.60	1.50					
е	_	_	0.65					
L	0.25	0.35	0.30					
L1	0.82	0.92	0.87					
K1	_	_	0.305					
K2	_	_	0.225					
Z	_	_	0.20					
All	Dimen	sions i	in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

U-DFN2020-6 (Type E)



Dimensions	value
Dilliensions	(in mm)
С	0.650
Х	0.400
X1	0.285
X2	1.050
Υ	0.500
Y1	0.920
Y2	1.600
Y3	2.300



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com