MMCX Straight Plug

multicomp PRO

RoHS


Compliant



Specifications

Frequency Range	: DC-6 GHz
Nominal Impedance	: 50 Ω
Max. Working Voltage	: 170 V
Proof Voltage	: 500 V
Max. VSWR	: 1.22
Operating Temperature Range	e : -55°C to +155°C
Bodies	: Brass per JIS-C3604
	Beryllium copper per ASTM B196 UNS C17300
Centre Contact	: Brass per JIS-C3604
Insulation	: PTFE per ASTM D1457 and ASTM D1710
Crimp Ferrule	: Brass per JIS-C2700

Diagram



No.	Description	Material	Finish	
1	Washer	Beryllium Copper		
2	Body	Brass	Gold 3µ″ Min.	
3	Insulation	PTFE	None	
4	Chassis	Brass	Gold 3µ″ Min.	
5	Centre Contact		Gold 30µ" Min.	
6	Crimp Ferrule		Gold	

Part Number Table

Description	Part Number
MMCX Straight Plug for use with RG178U RF Coaxial Cable	MP-37-01M-6-TGG

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility for such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

