




Relay Sockets SU series



One step wiring Easy & quick connection

IDEC CORPORATION

Push-in

Time saving & efficient

Wiring time reduced greatly compared with


conventional screw terminals.

(Compared with IDEC products) Approx. 55% reduced Push-in **SU Series** Conventional Screw terminal *) Based on IDEC research

Save up to 55% in wiring time


Reduce maintenance work

Push-in terminals eliminate the need for torque maintenance such as tightening of screws because screws are not used.




Wide range of options

Easy wiring to coil side connection using jumpers Can be used with polarized relays.



IDEC GT5Y timers can be mounted



GT5Y timer RU relay

Marking plate allows for easy identification

A marking plate enables easy identification of connections. Maintenance time is reduced.



One step wiring, easy & quick connection Safe and efficient SU series Push-in relay sockets



Highly reliable

High visibility


The terminal number on the socket can be clearly seen on the socket preventing incorrect wiring. Also, the distinct color pusher prevents a flat blade screwdriver from being inserted into the wire port.

Vibration-resistant

Safe and reliable Push-in connection achieves high contact reliablity and vibration resistance regardless of the wire size or shape.







Terminal no. (white) Pusher (orange)

Test point

Wire port

Hold-down spring (for relay) insert hole Release lever

Marking plate insert hole

IP20 Finger-safe

IEC60529 finger-safe design. IP20 protection. Safe contact protection structure prevents electric shock.



The release lever can be mounted to hold and remove the relay easily.





Push-in relay sockets reduce wiring by 55%*

* Compared with conventional screw terminal relay sockets.

Relay Sockets Package Quanti					
Shape	Part No. (Ordering No.)				
	2	SU2S-21L			
	4	SU4S-21L			

Specifications and Ratings

Part No.	SU2S-21L	SU4S-21L		
No. of Poles	2	4		
Rated Insulation Voltage	300V AC/DC			
Rated Thermal Current (*1)	12A	8A		
Applicable Wire	Solid wire / stranded wire: 0.14 to 1.5mm ² , AWG26 to 1 Stranded wire with ferrule 0.5 to 1.5mm ² , AWG20 to 16 Stranded wire with ferrule 0.14 to 1.0mm ² , AWG26 to 1	l6 (without insulated cover): 5 (with insulated cover):		
Insulation Resistance	100MΩ min. (500V DC meg	ger)		
Dielectric Strength	2500V AC, 1 min. (between live and dead metal parts, between live metal parts of the different poles)			
Vibration Resistance (Damage Limits)	10 to 55 Hz, amplitude 1.0 mm			
Shock Resistance (Damage Limits)	50G (when using SU9Z-S21R/-S21T hold-down spring or SU9Z-C21R release lever)			
Operating Temperature	–40 to +65°C (no freezing)			
Operating Humidity	5 to 85% RH (no condensation)			
Storage Temperature	Temperature -40 to +65°C (no freezing)			
Storage Humidity	5 to 85% RH (no condensation)			
Degree of Protection	IP20 (IEC 60529)			
Weight (approx.)	80g			
Applicable Standards	UL508, CSA C22.2 No.14, I	EC61984		


Applicable Relay / Timer

No. of Poles	Socket	Relay	Timer
2	SU2S-21L	RU2S	GT5Y-2
4	SU4S-21L	RU4S, RU42S	GT5Y-4

• For details on RU series relay, RN series relay, and GT5Y timer, see catalog.

• When using the SU socket with RU series relay, be sure to note the derating characteristics.

Derating Curve





*1) Be sure to note the derating characteristics.

All dimensions in mm.


Dimensions







31



F

E.

102

Note) The numbers in parentheses () are values accoring to NEMA standards.

Accessories

31

Function	Shape	Material	Part No.	Ordering No.	Remarks
Release Lever (For Relay)		Plastic	SU9Z-C21R	SU9Z-C21R	Note) Release lever cannot be used on timers.
Marking Plate		Plastic (white)	SU9Z-P2100W	SU9Z-P2100W	
Jumper		Bronze (tin-plated) Insulation: PBT plastic	SU9Z-J2102A	SU9Z-J2102A	A2 terminal of the coil is connected. The rated current is 2A.
Hold-down	For Relay	Stainless steel	SU9Z-S21R	SU9Z-S21R	See P.8 for Applicable Relay / Timer.
Spring	For Timer	Stainless steel	SU9Z-S21T		
DIN Rail		Aluminum	BAA1000	BAA1000	 Length: 1m Width: 35mm Weight: 200g (approx.)
End Clip	J. S. S.	Metal (zinc-plated steel)	BNL6	BNL-6	Weight: 15g (approx.) Use end clips when mounting multiple sockets on the DIN rail.
DIN Rail Spacer		Plastic (black)	SA-406B	SA-406B	Thickness: 5 mm Used for adjusting spacing between sockets mounted on a DIN rail.


When ordering, specify the Ordering No.

Instructions

Identifying the Socket

SU2S and SU4S can be identified by the part number marked on the side.

No. of Poles	Part No.
2	SU2S-21L
4	SU4S-21L



Applicable Wire

When wiring, use the applicable wires shown below.

Applicable Wire and Specifications

Applicable Wire (Stranded Wire, Solid Wire)	0.14 to 1.50mm² (AWG16 to 26)
Wire Strip Length (*1)	10 to 11mm
Ferrule Size (*2)	H0.5 to H1.5 (Without insulated cover)
(Weidmüller)	H0.14 to H1.0 (With insulated cover)
*1) Strip the sheath of the wire	

IO to 11 mm from the end

*2) When using a ferrule, refer to "Wire Size and Recommended Ferrule" below. Note: Make sure that the stranded wires do not loosen when using wiring without ferrules.

Wire Size and Recommended Ferrules

|--|

Applicable Wire (Stranded Wire)		Wire Strip Length	Part No.	
AWG	mm ²			
20	0.50	10 to 11 mm	H0.5/10	
18	0.75	10 to 11 mm	H0.75/10	
18	1.00	10 to 11 mm	H1.0/10	
16	1.50	10 to 11 mm	H1.5/10	

Ferrules with Insulated Covers

Applicable Wire (Stranded Wire)		Wire Strip Length	Part No.	
AWG	mm²			
26	0.14	10 to 11 mm	H0.14/12 GR SV	
24	0.25	10 to 11 mm	H0.25/12 HBL	
22	0.34	10 to 11 mm	H0.34/12 TK	
20	0.50	10 to 11 mm	H0.5/14 OR	
		12 to 13 mm	H0.5/16 OR	
18	0.75	10 to 11 mm	H0.75/14 W	
10	0.75	12 to 13 mm	H0.75/16 W	
18	1.00	10 to 11 mm	H1.0/14 GE	
10		12 to 13 mm	H1.0/16 GE	

Recommended Tools (Optional)

Name	Part No.
Crimping tool	PZ6 ROTO L
Flat blade screwdriver	SDS 0.4×2.5×75

Note 1) Note the crimping dimensions when using tools other than the recommended crimping tool. For details, see page 7.


Note 2) Use a flat blade screwdriver with a blade size of 0.4×2.5mm.

Refer to the table below for other companies' ferrules that correspond to "Wire Size and Recommended Ferrules".

Applicable Wire		PHOEN	IX CONTACT	WAGO		
(Strande	ed Wire)	Without	With	Without	With	
AWG	mm ²	Insulation Cover	Insulation Cover	Insulation Cover Insulation Cover		
26	0.14	—	AI 0.14-8 GY-1000	—	—	
24	0.25	_	AI 0.25-8 YE	—	FE-0.25-8N-YE	
22	0.34	—	AI 0.34-8 TQ	—	FE-0.34-8N-TQ	
20 0.50	0.50	A 0.5-8	AI 0.5-8 WH	FE-0.5-8	FE-0.5-8N-WH	
20 0.30		A 0.5-10	AI 0.5-10 EH	FE-0.5-10	FE-0.5-10N-WH	
18	0.75	A 0.75-8	AI 0.75-8 GY	FE-0.75-8	FE-0.75-8N-GY	
18 0.75		A 0.75-10	AI 0.75-10 GY	FE-0.75-10	FE-0.75-10N-GY	
18 1.00		A 1.0-8	—	FE-1.0-8	—	
10	1.00	A 1.0-10	_	FE-1.0-10	_	
16	1.50	A 1.5-10	_	FE-1.5-10	_	

Note) Check each company's catalog for details.

Parts Description



Inserting the Wire

Note: Two wire ports for each terminal

Wire with ferrule or solid wire

- 1) Insert the wire to the back of the wire port.
- 2) Wiring is complete. Pull the wire lightly to make sure that the wire does not pull out from the socket.



Stranded wire

- 1) Push the pusher (orange button) using a flat blade screwdriver.
- 2) Insert the wire fully in the wiring port while pressing the pusher
- 3) Release the flat blade screwdriver. Wiring is complete. Pull the wire lightly to make sure that the wire does not pull out from the socket.



Removing the Wire

- 1) Push the pusher using a flat blade screwdriver.
- 2) Pull out the wire while pressing the pusher.
- 3) Release the flat blade screwdriver.




Instructions

Note

- After wiring, tug lightly to make sure that the wire is properly connected.
- Operate the pusher with a force of 40N. Do not press excessively.
- Do not pull the wire out without depressing the pusher. When pulling the wire, be sure to pull in a straight direction. Otherwise, the socket may be damaged.
- Use a recommended flat blade screwdriver with the blade size of 0.4×2.5mm.
- When mounting multiple sockets on a DIN rail, be sure to secure both side with end clips (BNL6).

Crimping of Ferrules and Wiring

- Choose an appropriate ferrule for the wire.
- Cut the wire carefully to get a flat end.
- Make sure that ferrule sleeve is completely filled by the conductor. Depending on the cross section, the conductor should protrude approx. 0 to 1 mm from the ferrule sleeve. 0 to 1mm



• When crimping, refer to the instructions of the crimping tool.

Crimping dimensions: W2.4×H1.9 mm

Maximum connectable crimping size is W2.4×H1.9. Make sure that the ferrule size will be smaller than this dimension.




Note 1) If a tool other than the recommended crimping is used, the ferrule may not be crimped to the appropriate size and the clamp or spring inside the socket may be deformed and may not operate normally.

Note 2) Pin crimp terminals cannot be used.

Installing the Hold-down Spring

Use SU9Z-S21R (for relay) or SU9Z-S21R (for timer) hold-down springs. Install the hold-down springs into approriate spring insert hole. To install, see below diagram.



Confirm that the Hold-down Spring is securely installed into the spring insert hole. The relay Note) may fall off if it is not installed properly.

Installing / Removing the Relay

Installing the Relay

1. Unlock the release lever by pulling 2. Press the relay against the socket as down as shown with arrow ①

shown with arrow 2 Make sure that the relay is firmly in place.






Confirm that the relay is securely installed in the socket. The relay may fall off if it is not Note: installed properly.



Removing the Relay

Lightly press the relay to prevent it from falling off. Then pull down the release lever to the direction shown by the arrow and the remove the socket.





Note


Make sure that wire or finger is not caught between the release lever and socket. Because release lever is removable, make sure not to apply excessive force. Otherwise the relay may

Installing the Marking Plate

fall and result in damage.


Install the marking plate as shown in the diagram below. Mark on the durface using an oil-based marker, or affix a sticker with markings.

The size of the marking surface is 8.4mm × 25mm.




Using the Jumper

Insert the jumper to the back of the jumper slot. To remove, insert the small flat blade driver into the slot below and pull out. Because the rated current is 2A, use at 2A maximum.



Installing the Release Lever

To install the release lever, SU9Z-S21R (for relay), attach to the protrusion on the socket as shown below.



Applicable Relay / Timer

Applicable Relay (RU Series)

Ohama	Martal		Single Contact		Bifurcated Contact	Osil)/skana Oska	Coil Voltage	Coil Rat	
Shape		Model	Part No. (DPDT)	Part No. (4PDT)	Part No. (4PDT)	Coil Voltage Code *	Code	Gui nat	
		Standard	RU2S-*	RU4S-*	RU42S- *	A24, A100, A110, A200, A220,	A24	24V AC	
	ing	Stalluaru	11023- *	1043- *	10423- *	D6, D12, D24, D48, D100, D110	A100	100-110V AC	
	atchir ver	With diode (DC coil only)	RU2S-D- *	RU4S-D- *	RU42S-D- *	D6, D12, D24, D48, D100, D110	A110	110-120V AC	
TOTAL PARTY	With La Lev	With diode (DC coil only) Reverse polarity coil	RU2S-D1- *	RU4S-D1- *	RU42S-D1- *	D24	A200	200-220V AC	
Allows 17 South CD		With RC (AC coil only)	RU2S-R- *	RU4S-R- *	RU42S-R- *	A100, A110, A200, A220	A220	220-240V AC	
	hing	Ching a contract of the contra			104011	110420 11		D6	6V DC
			Standard	RU2S-C-*	RU4S-C-*	RU42S-C- *	A24, A100, A110, A200, A220, D6, D12, D24, D48, D100, D110	D12	12V DC
	atc		With diode (DC coil only)	RU2S-CD- *	RU4S-CD- *	RU42S-CD- *	D6, D12, D24, D48, D100, D110	D24	24V DC
	Without Lev	With diode (DC coil only)	RU2S-CD1- *	RU4S-CD1- *	RU42S-CD1- *	D24	D48	48V DC	
		/ith	Reverse polarity coil	N023-CD1- *	1043-001-*	10423-601-*	D24	D100	100V DC
	>	With RC (AC coil only)	RU2S-CR- *	RU4S-CR- *	RU42S-CR- *	A100, A110, A200, A220	D110	110V DC	

Applicable Timer (GT5Y)

Shape	Operation Mode	Contact Configuration	Output	Time Range	Operating Voltage	Part No.
A CONTRACTOR OF A CONTRACTOR O	A: ON Delay B: Interval ON C: Cycle OFF D: Cycle ON	2PDT	220V AC/ 30V DC, 5A	0.1S to 10H		GT5Y-2SN1A100
				0.1S to 30H	100 to 120V AC	GT5Y-2SN3A100
				0.1S to 60H		GT5Y-2SN6A100
				0.1S to 10H	– 200 to 240V AC –	GT5Y-2SN1A200
				0.1S to 30H		GT5Y-2SN3A200
				0.1S to 10H	12V DC	GT5Y-2SN1D12
				0.1S to 30H		GT5Y-2SN3D12
				0.1S to 60H		GT5Y-2SN6D12
				0.1S to 10H	24V DC	GT5Y-2SN1D24
				0.1S to 30H		GT5Y-2SN3D24
				0.1S to 60H		GT5Y-2SN6D24
		4PDT	220V AC/ 30V DC, 3A	0.1S to 10H	100 to 120V AC	GT5Y-4SN1A100
				0.1S to 30H		GT5Y-4SN3A100
				0.1S to 60H		GT5Y-4SN6A100
				0.1S to 10H	200 to 240V AC	GT5Y-4SN1A200
				0.1S to 30H		GT5Y-4SN3A200
				0.1S to 60H		GT5Y-4SN6A200
				0.1S to 30H	12V DC	GT5Y-4SN3D12
				0.1S to 10H	24V DC	GT5Y-4SN1D24
				0.1S to 30H		GT5Y-4SN3D24
				0.1S to 60H		GT5Y-4SN6D24



USA IDEC Corporation Tel: (408) 747-0550 opencontact@IDEC.com

Japan

IDEC Corporation

Tel: +81-6-6398-2527

United Kingdom

IDEC Electronics Ltd.

Tel: +44-1256-321000

sales@uk.IDEC.com

marketing@IDEC.co.jp

Canada IDEC Canada Ltd. Tel: (905) 890-8561 sales@ca.IDEC.com

Australia IDEC Australia Pty. Ltd. Tel: +61-3-8523-5900 sales@au.IDEC.com **IDEC** Think Automation and beyond...

www.IDEC.com

Germany IDEC Elektrotechnik GmbH Tel: +49-40-253054-0 service@IDEC.de

Hong Kong IDEC (H.K.) Co., Ltd. Tel: +852-2803-8989 info@hk.IDEC.com China/Beijing IDEC (Beijing) Corporation Tel: +86-10-6581-6131

China/Shanghai IDEC (Shanghai) Corporation Tel: +86-21-6135-1515 idec@cn.IDEC.com

Technical support:

support@idec.com

Sales support:

sales@idec.com

Rated Coil Voltage

ting

China/Shenzhen IDEC (Shenzhen) Corporation Tel: +86-755-8356-2977

Singapore IDEC Asia Pte. Ltd. Tel: +65-6746-1155 info@sg.IDEC.com

Taiwan IDEC Taiwan Corporation Tel: +886-2-2698-3929 service@tw.IDEC.com

©2021 IDEC Corporation. All Rights Reserved. Catalog No. EP1720-USA01

Specifications and other descriptions in this catalog are subject to change without notice.