2383942-2 - ACTIVE

TE Internal #: 2383942-2 PCB Terminal Blocks, Header, Wire-to-Board, 2 Position, 3.5mm [. 13in] Centerline, 1 Row, Side Wire Entry Angle, 28 – 16AWG Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: Header

Connector System: Wire-to-Board

Number of Positions: 2

Centerline (Pitch): 3.5 mm [.13 in]

Number of Rows: 1

Features

Product Type Features



Wire Protection	With
Block Type	PCB Mount
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
Threaded Flange	Without
Stacked Levels	Level 1
Stacking Configuration	Side Stackable
Number of Positions	2
Number of Rows	1
Wire Entry Angle	Side
Electrical Characteristics	
Current Rating (Max)	12 A

2383942-2

PCB Terminal Blocks, Header, Wire-to-Board, 2 Position, 3.5mm [.13in] Centerline, 1 Row, Side Wire Entry Angle, 28 – 16AWG Wire Size



Voltage Rating	300 VAC
Body Features	
Interlock	Without
Color	Black
Contact Features	
Contact Mating Area Plating Material	Tin
Contact Mount	Surface Mount
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	12 A
Mechanical Attachment	
Screwless Terminal Block	No
Mounting Angle	Vertical
Screw Size	M3
Screw Plating Material	Tin
Screw Material	Copper Alloy
Screw Flange	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Black
Housing Material	High Temperature Polyamide
Centerline (Pitch)	3.5 mm[.13 in]
Dimensions	
Wire Size	.08 – 1.31 mm²
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Packaging Features	
Packaging Method	Tape & Reel
Packaging Quantity	300

Product Compliance

C For support call+1 800 522 6752

2383942-2

PCB Terminal Blocks, Header, Wire-to-Board, 2 Position, 3.5mm [.13in] Centerline, 1 Row, Side Wire Entry Angle, 28 – 16AWG Wire Size



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Clamp) Aticle Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-onreach

Compatible Parts



Documents

Product Drawings TERMI-BLOK SMD MOUNT 180_2P_3.5 MM

English

CAD Files 3D PDF

C For support call+1 800 522 6752

2383942-2

PCB Terminal Blocks, Header, Wire-to-Board, 2 Position, 3.5mm [.13in] Centerline, 1 Row, Side Wire Entry Angle, 28 – 16AWG Wire Size



3D

Customer View Model ENG_CVM_CVM_2383942-2_1.2d_dxf.zip English Customer View Model ENG_CVM_CVM_2383942-2_1.3d_igs.zip English Customer View Model ENG_CVM_CVM_2383942-2_1.3d_stp.zip English

Datasheets & Catalog Pages Board Mount Reflow Terminal Block

English

Product Specifications Application Specification

English