

Cyanolube

Product Code: CYL

PRODUCT DESCRIPTION

Electrolube Cyanolube is a one part, air drying, low viscosity cyanoacrylate adhesive. It offers fast cure speed together with high final cured bond strength and will bond a wide variety of substrates.

Nitrile, Neoprene and natural rubbers can be bonded in 1-2 seconds. Plastics such as ABS, flexible PVC, Polyacetal, EPT and EVA all bond in 1-2 seconds. Metals such as Steel, Aluminium, Copper and Brass all bond in under 5 seconds .

TYPICAL PROPERTIES

LIQUID MATERIAL

Colour:	Clear
Flash Point:	> 85 °C
Cure Speed:	1 - 5 seconds
Viscosity:	20 cps
SG:	1.06
Max Operating Temp:	-60 to 90 °C

CURED MATERIAL

Full Cure Time:	24 hours
Tensile Strength:	25 - 30 N/mm
Tensile Shear Strength:	15 N/mm

DIRECTIONS FOR USE

For optimum results, clean and abrade the surfaces to be bonded and make sure they are free from dirt, dust and contamination (such as mould release agents). Apply a thin film or drop of **Cyanolube** to one surface only and bring the parts together, holding firmly for a few seconds.

One drop will bond about 25 square mm.

TECHNICAL
DATA
SHEET



**Copyright
Electrolube
2003**

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



Cyanolube – Page 2

PACKAGING

Cyanolube 5 ml in 6 pack

ORDER CODE

CYL05BE

TECHNICAL
DATA
SHEET



Copyright Electrolube 2003

All information is given in good faith but without warranty.

Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

