




TE Internal #: TAX38821112-004

M8/M12 Cable Assemblies, Industrial Ethernet, Ethernet, 8 Positions, X M8/M12 Cable Assembly Keying, Plug/Plug, M12 to M12, Straight-Right Angle

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies



M8/M12 Application Type: **Industrial Ethernet**

Number of M8/M12 Cable Assembly Positions: **8**

Industrial Protocols: **Ethernet**

M8/M12 Cable Assembly Keying: **X**

M8/M12 Cable Assembly Connector Type: **Plug/Plug**

Features

Product Type Features

| | |
|--------------------------------------|----------------|
| LED | Without |
| Cable Type | PVC |
| Product Type | Cable Assembly |
| Assembly Type | Overmolded |
| M8/M12 Cable Assembly Connector Type | Plug/Plug |
| M8/M12 Cable Assembly Type | M12 to M12 |
| M8/M12 Cable Assembly Shielded | Yes |

Configuration Features

| | |
|---|--------------|
| Number of M8/M12 Cable Assembly Positions | 8 |
| M8/M12 Cable Assembly Keying | X |
| M8/M12 Cable Assembly Configuration | Double Ended |

Electrical Characteristics

| | |
|-------------------|--------|
| Operating Voltage | 30 VDC |
|-------------------|--------|

Body Features

| | |
|--|--|
| | |
|--|--|



| | |
|--------------------------|--------------|
| Connector Color | Black |
| Environmental Protection | IP67 |
| Conductor Material | Copper Alloy |
| Cable Jacket Color | Green |

Mechanical Attachment

| | |
|--------------------------------------|----------------------|
| M8/M12 Cable Assembly Mounting Angle | Straight-Right Angle |
|--------------------------------------|----------------------|

Housing Features

| | |
|--|-----------|
| M8/M12 Cable Assembly Housing Material | PA66+25GF |
|--|-----------|

Dimensions

| | |
|--------------------------------|---------|
| Overall Outside Cable Diameter | 6.9 mm |
| Wire Size | 26 AWG |
| Cable Assembly Length | 3000 mm |

Operation/Application

| | |
|-------------------------|---------------------|
| M8/M12 Application Type | Industrial Ethernet |
|-------------------------|---------------------|

Industry Standards

| | |
|----------------------|----------|
| Industrial Protocols | Ethernet |
|----------------------|----------|

Packaging Features

| | |
|--------------------|-----|
| Packaging Method | Bag |
| Packaging Quantity | 5 |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Not Yet Reviewed |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as

EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Documents

Product Drawings

[RPC-M12X-8MS-3.0SH-M12X-8MR-PVC](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_TAX38821112-004_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TAX38821112-004_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TAX38821112-004_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Virtual Sample Kit - M12 X-Code-Cordsets](#)

English

Product Specifications



Application Specification

English