

Mushroom Head Emergency Stop Switches



RB2-B554



RB2-BT4



RB2-B514


Standards:	IEC 947-5-1/EN 60947-5-1 UL 508, CSA C-22-2 n° 14
Approvals:	UL & CSA RoHS Compliant
Protection:	IP65
Temperature:	-40°C to +70°C (Storage) -25°C to +70°C (Working)
Vibration Resistance:	8gn
Shock Resistance:	15gn
Mechanical Life:	300,000 operations

AC Ratings, Inductive - NEMA A600
35% Power Factor

Volts	Make Amperes	VA	Break Amperes	VA	Continuous carrying Amperes	Resistive factor Make, Break & continuous	75% Power factor Make, Break & Amperes
120	60	7200	6	720	10		10
240	30	7200	3	720	10		10
480	15	7200	1.5	720	10		10
600	12	7200	1.2	720	10		10

DC Ratings, NEMA Type Q600
Inductive and resistive

Volts	Make & Break	Continuous
125	55	2.5
250	0.27	2.5
600	0.10	2.5



The above graph and AC / DC ratings tables refer to contact block characteristics:

RB2-BE101 (Normally Open) / RB2-BE102 (Normally Closed)