

3.0mm (1.2") 8×8 White Dot Matrix LED Displays Technical Data Sheet

Model No.: KWM-30881XWB-Y

http://www.luckylightled.com



Features:

- ♦ 1.2inch (32.00mm) Matrix height.
- \diamond Colors: white.
- ♦ Flat package and light weight.
- \diamond Easy assembly.
- $\diamond~$ High quality and low cost.
- $\diamond~$ High reliable and intensity.
- \diamond Low power requirement.
- $\diamond~$ The product itself will remain within RoHS compliant version.

Descriptions:

- ◇The KWM-30881 series is a large emitting area (3.0mm diameter) LED sources configured in a 64 dots 8*8 matrix array.
- $\diamond These devices are made with yellow dots and black surface.$

Applications:


- ◊ Audio equipment.
- ◊ Instrument panels.
- ♦ Digital read out display.

Device Selection Guide:

Model No.	Chip Material	Face Color	Descriptions
KWM-30881AWB-Y	In CoN	Black	Row Anode
KWM-30881CWB-Y	InGaN	Black	Row Cathode



Package Dimension:



Spec No: W12088A/BRev No: V.2Approved: JoJoChecked: SunLucky Light Electronics Co., Ltd.

Date: Mar/25/2008 Drawn: Liu Page: 3 OF 6

http://www.luckylightled.com



Absolute Maximum Ratings at Ta=25℃

Parameters	Symbol	Max.	Unit
Power Dissipation Per Dot	PD	100	mW
Peak Forward Current Per Dot (1/10 Duty Cycle, 0.1ms Pulse Width)	IFP	100	mA
Forward Current Per Dot	IF	25	mA
Dating Linear From 50℃		0.4	mA/°C
Reverse Voltage	VR	5	V
Operating Temperature Range	Topr	-40℃ to +80℃	
Storage Temperature Range	Tstg	-40℃ to +85℃ 260℃ for 5 Seconds	
Soldering Temperature	Tsld		


Electrical Optical Characteristics at Ta=25 $^\circ\!\!\!\mathrm{C}$


Parameters	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity (Note 1) *	IV	45.0	90.0		mcd	IF=20mA
Luminous Intensity Matching Ratio (Dot To Dot)	I _{v-m}			2:1		IF=10mA
Chromaticity Coordinates	Х		0.28			IF=20mA
(Note 2)	Y		0.29			
Forward Voltage	VF		3.2	4.0	V	IF=20mA
Reverse Current	IR			50	μA	$V_R = 5V$

Notes:

- 1. Luminous Intensity Measurement allowance is \pm 10%.
- 2. It use many parameters that correspond to the CIE 1931 2°. X, Y, and Z are CIE 1931 2° values of Red, Green and Blue content of the measurement.







Lucky Light Electronics Co., Ltd.

http://www.luckylightled.com



Please read the following notes before using the datasheets:

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

2.1 If the package contains a moisture proof bag inside, please don't open the package before using.

2.2 Before opening the package, the LEDs should be kept at 30° C or less and 80° RH or less.

2.3 The LEDs should be used within a year.

2.4 After opening the package, the LEDs should be kept at 30° C or less and 60%RH or less.

3. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 260°C for 5 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

4. Soldering

When soldering, for Lamp without stopper type and must be leave a minimum of 3mm clearance from the base of the lens to the soldering point.

To avoided the Epoxy climb up on lead frame and was impact to non-soldering problem, dipping the lens into the solder must be avoided.

Do not apply any external stress to the lead frame during soldering while the LED is at high temperature.

Recommended soldering conditions:

Soldering Iron		Wave Soldering		
Temperature Soldering Time	300℃ Max. 3 sec. Max. (one time only)	Pre-heat Pre-heat Time Solder Wave Soldering Time	100℃ Max. 60 sec. Max. 260℃ Max. 5 sec. Max.	

Note: Excessive soldering temperature and / or time might result in deformation of the LED lens or catastrophic failure of the LED.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used . It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

6. Caution in ESD

Static Electricity and surge damages the LED. It is recommended to use a wrist band or anti-electrostatic glove when handling the LED. All devices equipment and machinery must be properly grounded.